

Triple-Monitor USB-C Docking Station, 140W Laptop Charging Dock for MacBook Pro and Windows, 4K 60Hz HDMI or DisplayPort, TAA

Product ID: DK30C2DPEPRUE



This universal docking station offers high-resolution display support and broad OS compatibility to simplify device management and user experience, making it ideal for modern professional workspaces including hot desks and mixed-device environments.

Support up to three 4K 60Hz monitors via USB-C while delivering up to 140W of power to high-performance laptops. A USB-A adapter extends compatibility to legacy systems, enabling flexible dual-display setups in shared workstations and hybrid IT environments.

DisplayLink-based HDMI and DisplayPort outputs enable multi-monitor setups on macOS, Windows, and ChromeOS. The USB-C video output port leverages the laptop's built-in GPU to deliver high-performance video output. A unified driver experience simplifies hot desk provisioning, reduces IT support overhead, and ensures consistent performance across transient and mobile workstations.

The integrated 2.5GbE port ensures high-speed data transfers and supports PXE Boot, Jumbo Frames, and Wake-on-LAN. Built-in lock slots and optional mounting solutions (SSPMSUDWM, DOCK-NUC-VESA-MOUNT, SSPMSVESA) enhance the physical security of the docking station.

Certifications, Reports and Compatibility





Applications

Features

- **Universal 140W USB-C Dock:** Supports triple 4K 60Hz displays and delivers up to 140W power over USB-C for high-performance laptops; USB-A adapter offers legacy host compatibility with dual-display support, ensuring flexibility across deployments
- **Cross Platform Support:** Streamline deployment across diverse environments with DisplayLink-based HDMI and DisplayPort outputs; USB-C video output utilizes the laptops GPU for higher video performance; Multi-monitor support for macOS, Windows, and ChromeOS
- **2.5G Ethernet for High-Speed Networking:** Transfer large files or work directly from the cloud with a reliable 2.5GbE connection; Supports Jumbo Frames for lower CPU overhead and improved throughput, plus PXE Boot and Wake-on-LAN for IT-managed deployments
- **Mounting and Security:** Universal dock features built-in lock slots for physical security; Supports surface or VESA mounting to keep the dock secured and out of the way (mounting accessories sold separately: SSPMSUDWM, DOCK-NUC-VESA-MOUNT, SSPMSVESA)
- **The IT Pro's Choice:** Our docking stations are rigorously tested in our Innovation Lab to ensure enterprise-grade reliability and cross-platform compatibility; Built to support large-scale deployments, Windows 11 upgrades, and the shift to AI-enabled PCs

General

UPC	065030912945
Package Quantity	1
Warranty	3 Years

Special Notes / Requirements

Special Notes	USB 3.2 Gen 2 (10Gbps) is also known as USB 3.1 Gen 2 (10Gbps) USB 3.2 Gen 1 (5Gbps) is also known as USB 3.1 Gen 1 (5Gbps) and USB 3.0 (5Gbps)
---------------	---

Jumbo Frames are no longer supported in macOS

Power

Power Source	AC Adapter Included
Power Delivery	140W
Input Voltage	110V-240V AC
Input Current	2.5A
Output Voltage	20V DC
Output Current	10.5
Center Tip Polarity	Positive
Plug Type	M
Power Consumption	210W

Physical & Environmental

Color	Space Gray
Product Length	9.2 in [23.3 cm]
Product Width	3.3 in [84 mm]
Product Height	1.5 in [37 mm]
Weight of Product	13.9 oz [394 g]
Operating Temperature	0C to 40C (32F to 104F)
Storage Temperature	-20C to 70C (-4F to 158F)
Humidity	0% ~ 90% RH (non-condensing)

Performance

Supported Charging Outputs	BC 1.2 (1.5A)
	USB-C (18W)
Maximum Data Transfer Rate	10Gbps
Type and Rate	USB 10Gbps

UASP Support	Yes
Compatible Networks	2.5G/1G/100Mbps/10Mbps
Full Duplex Support	Yes
PXE	Yes
Wake-On-LAN (WOL)	Yes
MTBF	42,209 Hours
Maximum Digital Resolutions	4K 60Hz

Hardware

Fast-Charge Port(s)	Yes
4K Support	Yes
Displays Supported	3
Number of Battery Charge 1.2 Ports	1
Audio	Yes
Interface	USB 3.2 Gen 2 10Gbps
Compatible Lock Slot	Kensington K-Slot Kensington Nano Slot Noble Wedge Slot
Number of Displays	3
Chipset ID	DisplayLink - DL6950 Genesys Logic - GL5911 Genesys Logic - GL5910 Genesys Logic - GL3590 Realtek - RTL8156B
LED Indicators	1 - LAN Port - Network Status LED (Green): Illuminates to Indicate an Ethernet Link is Active 1 - LAN Port - Network Activity LED (Amber): Blinks to Indicate

Network Traffic

1 - Power Button LED (White): Illuminates when the Dock is Connected to a Power Source and Powered On

Packaging & In-the-Box

Included in Package	1 - Docking Station
	1 - 3ft (1m) USB-C Host Cable
	1 - Universal Power Adapter
	1 - Power Cable
	1 - Product Documentation
Package Width	9.9 in [25.1 cm]
Package Depth	6.7 in [16.9 cm]
Package Height	3.5 in [90 mm]
Shipping (Package) Weight	2.7 lb [1.2 kg]

Connector(s)

Host Connector 1 (Quantity)	1
Host Connector 1	USB-C
Connector 1 (Quantity)	1
Connector 1	USB-A (5Gbps, 4.5W)
Connector 2 (Quantity)	1
Connector 2	USB-A (5Gbps, 7.5W)
Connector 3 (Quantity)	1
Connector 3	USB-C (5Gbps, 18W)
Connector 4 (Quantity)	1
Connector 4	3.5mm (4 Conductors, TRRS)
Connector 5 (Quantity)	1

Connector 5	RJ-45
Connector 6 (Quantity)	2
Connector 6	DisplayPort
Connector 7 (Quantity)	2
Connector 7	HDMI
Connector 8 (Quantity)	2
Connector 8	USB-A (480Mbps, 2.5W)
Connector 9 (Quantity)	1
Connector 9	USB-C (10Gbps, 4.5W)
Connector 10 (Quantity)	1
Connector 10	USB-C Dual-Mode DP++ (10Gbps, 7.5W / DP Alt-Mode)

****Product appearance and specifications are subject to change without notice.***