

2 Port CardBus RS232 Serial Laptop PC Adapter Card - 16950

Product ID: CB2S950



This CardBus RS232 Serial Laptop PC Adapter Card adds two RS232 serial ports to a notebook computer, letting you connect your mobile computer to serial peripheral devices.

Supporting data transfer rates of up to 921.6 Kbps, the RS232 serial adapter features a high performance 16950 UART chipset, ensuring flawless connectivity with your serial peripherals.

The adapter is backed by StarTech.com's Lifetime Warranty and free, lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Works with serial modems, POS devices, PDAs, digital cameras, printers, ISDN terminal adapters, and more.
- Connect up to 2 RS-232 serial devices to a CardBus slot on your notebook.

Features

- 128-byte deep FIFO data buffer
- High Performance 16C950 UART with maximum data transfer rate up to 921.6 Kbps
- Offers 2 DB9 RS-232 ports to connect multiple devices to a notebook PC

Hardware

Warranty	Lifetime
Ports	2
Interface	Serial
Bus Type	CardBus (PCMCIA)
Port Style	Dongle (Included)
Chipset ID	PLX/Oxford - OX16PCI952

Performance

Serial Protocol	RS-232
Max Baud Rate	921.6 Kbps
FIFO	128 Bytes

Connector(s)

Connector Type(s)	PC Card (Type II, Cardbus)
External Ports	DB-9 (9 pin, D-Sub)

Software

OS Compatibility	Windows 8 / 8.1 (32/bit), 7 (32/64), Vista (32/64), XP (32/64), 2000, ME, 98SE, 95 Windows Server 2012, 2008 R2, 2003 (32/64) Linux 3.5
------------------	---

Environmental

Operating Temperature	-10C to 80C (14F to 176F)
Storage Temperature	-20C to 100C (-4F to 212F)
Humidity	5~85% RH

Physical Characteristics

Product Length	4.7 in [12 cm]
Product Width	2.4 in [60 mm]
Product Height	0.9 in [24 mm]
Weight of Product	8.8 oz [250 g]



**Packaging
Information**

Package Length	8.1 in [20.7 cm]
Package Width	5.5 in [14 cm]
Package Height	1.5 in [38 mm]
Shipping (Package) Weight	9.9 oz [280 g]

What's in the Box

Included in Package	CardBus Serial Card
	2 Port DB9 Breakout Cable
	Driver CD
	Instruction Manual

****Product appearance and specifications are subject to change without notice.***

