

3ft (91cm) DisplayPort 2.1 Cable, VESA Certified DP80 DisplayPort Cable w/UHBR20/HDR/DSC 1.2a/HDCP 2.2, 16K/8K 60Hz, 4K 240Hz, 80Gbps, DP 2.1 Cable, UHD Monitor Cord, M/M

Produkt-ID: DP21-3F-DP80-CABLE



Connect a 16K/8K UHD DisplayPort monitor to a host computer or MST hub, using this VESA-Certified DisplayPort 2.1 DP80 Cable. This cable facilitates high bandwidth video and multi-channel audio and is ideal for 16K/8K workstations, high performance GPUs, and dedicated AV applications including media production and content creation.

For seamless operation between DisplayPort-enabled devices, the DisplayPort 2.1 Cable is VESA Certified for guaranteed DP 2.1 and backward compatibility (DP 2.0/1.4/1.2). It supports G-Sync and FreeSync, enhancing Variable Refresh Rate (VRR) performance for optimal picture quality between high-capacity GPUs and supported displays.

This DisplayPort cable features a flexible TPE outer jacket that is tested to withstand 600 bending cycles at +/-60 degrees, and routes easily around corners and desk edges. Robust strain reliefs enable convenient positioning of the cable, and latching nickel-plated DP connectors attach securely to prevent accidental disconnection. The connectors are rated to operate beyond 10,000 insertions.

This DP80 DisplayPort cable supports the following DP 2.1 features:

- Resolutions up to 16K 60Hz w/DSC, using a compatible DP source and display
- UHBR20 supports high refresh rates including 8K 85Hz, 4K 240Hz, and 1440p 240Hz
- High-Bandwidth Digital Content Protection (HDCP) 2.2 for a secure connection between source and display
- High Dynamic Range 10 (HDR10) for higher contrast ratio and vibrant picture quality
- Display Stream Compression (DSC) 1.2a for maximum resolution output

- Multi-Stream Transport (MST) for daisy-chaining multiple monitors
- 32 Uncompressed Digital Audio Channels
- Backward compatible with previous DP versions

This DP 2.1 Cable is constructed with braided aluminum mylar shielding to minimize EMI for clear, consistent audio/video output and long-term reliable performance.

Zertifikate Berichte und Kompatibilität



Anwendungen

- Facilitate full-featured DisplayPort 2.1 performance with backward compatibility
- Connect a high performance GPU to an 8K 60Hz UHD display

Merkmale

- **HIGH PERFORMANCE:** DP 2.1 Cable is designed for UHBR20-enabled DisplayPort devices; DP80 (80Gbps) supports up to 16K 60Hz video w/DSC and 32-channel audio; Latching DP connectors; Flexible TPE jacket routes easily through tight spaces
- **FULL DP COMPATIBILITY:** DP 2.1 Cable is VESA certified for guaranteed performance and compatibility with DP 2.1 devices, ensuring reliable signal consistency and smooth video playback on any DisplayPort display; Backward compatible with DP 2.0/1.4/1.2
- **QUALITY CONSTRUCTION:** Nickel-plated ends rated beyond 10,000 insertions; Latching DP connectors prevent accidental disconnections; Shielded coaxial wire for enhanced EMI protection; Durable TPE Jacket and strain reliefs are halogen-free and RoHS compliant
- **APPLICATIONS:** Ideal for high resolution 16K/8K displays; Up to 240Hz refresh rate at 4K resolution; Suitable for high performance GPUs and AV workstations; Supports MST multi-monitor daisy chains; Connect a DP monitor to a UHD docking station
- **SPECS:** Black; 3-foot; VESA-Certified DisplayPort 2.1; Supports UHBR20/HDR/MST/DSC 1.2/HDCP 2.2; DP80 (80Gbps); 16K 60Hz w/DSC, 8K 85Hz, 4K 240Hz; 32-ch Audio; Compatible w/DP 2.0/1.4/1.2; Latching DP Connectors; 30AWG Coaxial Wire; 5.8mm (0.23in) O.D.

Garantiebestimmungen	Lifetime
Active or Passive Adapter	Passiv
Steckverbinderplatten	Nickel
Typ der Kabelummantelung	TPE - Thermoplastic Elastomers
Typ der Kabelabschirmung	Aluminium-Mylar-Folie mit Geflecht
Feuerwiderstandssklasse	VW-1e
Kabeltyp	Passive Copper Cable
Industrienormen	DisplayPort 2.1

Leistung

Video Revision	DisplayPort 2.1
Max. Datenübertragungsrate	80Gbps
Audiospezifikationen	DisplayPort - 32 Channel Audio

Steckverbinder

Steckverbinder A	1 - DisplayPort
Steckverbinder B	1 - DisplayPort

Umgebungsbedingungen

Betriebstemperatur	0°C to 45°C (32°F to 113°F)
Lagertemperatur	-20°C to 70°C (-4°F to 158°F)
Feuchtigkeit	10%~85% RH

Physische Eigenschaften

Farbe	Schwarz
Steckverbinderart	Gerade

Drahtstärke	30 AWG
Gehäusotyp	ABS
Kabellänge	3.0 ft [0.9 m]
Außendurchmesser des Kabels	0.2 in [5.8 mm]
Produktlänge	36.9 in [93.7 cm]
Produktbreite	0.8 in [2.1 cm]
Produkthöhe	0.4 in [1.1 cm]
Produktgewicht	2.4 oz [68.0 g]

Verpackungsinformationen

Paketlänge	4.6 in [11.7 cm]
Paketbreite	5.0 in [12.7 cm]
Pakethöhe	1.0 in [2.6 cm]
Versandgewicht (Verpackung)	2.9 oz [82.0 g]

Verpackungsinhalt

Im Paket enthalten	1 - 1m DisplayPort 2.1 Kabel
--------------------	------------------------------

Garantieinformationen

Warranty	Lifetime
----------	----------

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.