

3ft/1m USB C to VGA Cable - 1920x1200/1080p USB Type C to VGA Video Active Adapter Cable - Thunderbolt 3 Compatible - Laptop to VGA Monitor/Projector - DP Alt Mode HBR2

Product ID: CDP2VGAMM1MB



This USB-C to VGA cable lets you connect your Thunderbolt 3 or USB Type-C enabled device to your computer monitor with just one cable, providing you with a convenient, clutter-free solution.

The USB-C to VGA adapter cable lets you harness the video capabilities that are built into your computer's USB-C connection, to deliver astonishing resolutions up to 1920 x 1200.

Plus, the adapter is backward compatible with 1080p displays, which makes it a great accessory for home, office or other work environments.

At 3.3 ft. (1 m) in length, this computer monitor cable delivers a compact connection that eliminates excess adapters and cabling, ensuring a tidy, professional installation. For longer installations, we also offer a 6.6 ft. (2 m) (CDP2VGAMM2MB) and a 9.8 ft. (3 m) (CDP2VGA3MBNL) USB-C to VGA cable, enabling you to choose the right cable length for your custom installation needs.

The reversible USB-C connector offers an easy and convenient connection. To ensure an easy operation and installation, this USB-C to VGA cable works with both Windows and Mac computers and supports plug-and-play installation.

CDP2VGAMM1MB is backed by a 3-year StarTech.com warranty and free lifetime technical support.

Note: Your USB-C port must support DisplayPort over USB-C (DP Alt Mode) in order to work with this adapter.

Certifications, Reports and Compatibility





Applications

- Connect USB-C or Thunderbolt 3 devices to VGA displays
- Ideal for home office or work desk environments
- Experience enhanced imaging with support for 1920x1200

Features

- **DIGITAL TO ANALOG:** 3.3ft/1m USB-C (DP 1.2 Alt Mode HBR2) active adapter cable connects a single VGA display supporting 1920x1200 & 1080p at 60Hz EDID & DDC pass-through Thunderbolt 3 compatible
- **INTEGRATED VIDEO ADAPTER CABLE:** Male to Male Adapter Cable reduces clutter, minimizes signal loss and potential failure points making it ideal for fixed workstations in your home, office or classroom
- **COMPUTER COMPATIBILITY:** Dell XPS Precision Latitude, Lenovo ThinkPad X1 Carbon Extreme, Surface Pro 7/Laptop 3/Book 3, MacBook Pro, iPad Pro, TB3 MacBook Air, HP EliteBook Spectre ZBook & Chromebooks
- **DISPLAY COMPATIBILITY:** Tested w/ range of 1080p VGA monitors incl brands like Dell, Samsung, Asus, Acer, & LG and projectors like Sony, Christie, LG, NEC & Epson
- **EASY TO USE:** Video adapter cable has been tested to ensure compatibility w/ USB Type C DP Alt Mode or TB3 devices; driverless plug & play setup w/ macOS, iPadOS, Windows 10, Linux, Chrome OS & Android

Hardware

Warranty	3 Years
AV Input	USB-C
Ports	1
AV Output	VGA
Chipset ID	Via Labs - VL103 NXP - PTN3355

Performance

Maximum Analog Resolutions	1920x1200 or 1080p
Supported Resolutions	1024x768

1280x720 (High-definition 720p)
1920x1080 (High-definition 1080p)
1920x1200

Wide Screen Supported Yes
Audio Specifications VGA - No Audio Support

Connector(s)

Connector A 1 - USB-C (24 pin) DisplayPort Alt Mode
Connector B 1 - VGA (15 pin, High Density D-Sub)

Special Notes / Requirements

System and Cable Requirements Your USB-C port must support DisplayPort over USB-C (DP Alt mode) in order to work with this adapter.
Note Your USB-C port must support DisplayPort over USB-C (DP Alt mode) in order to work with this adapter.

Environmental

Operating Temperature 0C to 70C (32F to 158F)
Storage Temperature -10C to 80C (14F to 176F)
Humidity 5~90% RH (Non-condensing)

Physical Characteristics

Color Black
Accent Color Black
Cable Length 3.3 ft [1 m]
Product Length 3.4 ft [1.0 m]
Product Width 1.4 in [3.5 cm]
Product Height 0.6 in [1.5 cm]
Weight of Product 3.3 oz [93.0 g]

Packaging Information

Package Quantity	1
Package Length	8.9 in [22.5 cm]
Package Width	4.9 in [12.5 cm]
Package Height	0.4 in [1.0 cm]
Shipping (Package) Weight	3.5 oz [99.0 g]

What's in the Box

Included in Package	1 - USB-C to VGA adapter cable
---------------------	--------------------------------

****Product appearance and specifications are subject to change without notice.***