

3ft (91cm) DisplayPort to DVI Converter Cable - 1920x1200

Product ID: DP2DVI2MM3



This 3-foot DisplayPort to DVI-D adapter cable lets you connect your DisplayPort (DP) equipped Ultrabook, laptop or desktop computer to a DVI monitor or projector with no additional adapters or cables required. The passive adapter supports video resolutions up to 1920x1200 (WUXGA), perfect for high-resolution applications.

For the simplest and most discreet installation, this DP to DVI-D adapter connects directly from your DisplayPort video source to the DVI port on your display. It doesn't need a power source, unlike some converter dongles that require active power and separate bulky video cabling.

With this DP to DVI cable, you can bridge the gap between old and new technologies by converting your existing DVI display to work with your DP video source.

Upgrading every component in your A/V setup can be costly and time consuming. This cost-effective adapter lets you save the expense and hassle of buying a new display, by ensuring your existing DVI display will work with your DisplayPort equipment.

This 3 ft. adapter cable delivers a compact connection that eliminates excess to ensure a tidy, professional installation. For longer installations, we also offer a 6 ft DP to DVI cable (DP2DVIMM6), enabling you to choose the right cable length for your custom installation needs.

The DP2DVI2MM3 is backed by a 3-year StarTech.com warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Connect a DisplayPort video source directly to any DVI-D (digital) display with no additional adapters required
- Re-purpose an existing DVI display for use with a new DisplayPort-equipped computer, or as a secondary display
- Ideal for digital entertainment centers, home offices, business conference rooms and trade show displays

Features

- Reduce clutter with a compact 3ft adapter cable
- Avoid upgrades by keeping your DVI display
- Avoid the hassle of converters that require additional cabling and power adapters with a plug-and-play cable adapter
- Supports PC resolutions up to 1920x1200 and HDTV resolutions up to 1080p
- Easy to use cable, no software required

Hardware

| | |
|---------------------------|--------------------------|
| Warranty | 3 Years |
| Active or Passive Adapter | Passive |
| AV Input | DisplayPort - 1.2 |
| AV Output | DVI-D - Single-Link |
| Audio | No |
| Connector Plating | Gold |
| Cable Jacket Material | PVC - Polyvinyl Chloride |

Performance

| | |
|-----------------------------|------------------------|
| Maximum Digital Resolutions | 1920x1200 / 1080p |
| Audio Specifications | DVI - No Audio Support |
| MTBF | 2,405,577 hours |

Connector(s)

| | |
|-------------|--------------------------|
| Connector A | 1 - DisplayPort (20 pin) |
| Connector B | 1 - DVI-D (25 pin) |

Special Notes / Requirements

| | |
|-------------------------------|--|
| System and Cable Requirements | DP++ (DisplayPort++) port is required on video card or video source for DVI and HDMI pass-through. |
|-------------------------------|--|

Environmental

| | |
|-----------------------|-------------------------|
| Operating Temperature | 5C to 35C (41F to 95F) |
| Storage Temperature | 0C to 70C (32F to 158F) |
| Humidity | 20~80% RH |

Physical Characteristics

| | |
|-------------------|-------------------|
| Color | Black |
| Cable Length | 36.0 in [914 mm] |
| Product Length | 36.0 in [91.4 cm] |
| Product Width | 1.6 in [4.0 cm] |
| Product Height | 0.6 in [1.5 cm] |
| Weight of Product | 2.8 oz [80.0 g] |

Packaging Information

| | |
|---------------------------|------------------|
| Package Quantity | 1 |
| Package Length | 5.0 in [12.8 cm] |
| Package Width | 7.8 in [19.8 cm] |
| Package Height | 0.8 in [2.1 cm] |
| Shipping (Package) Weight | 3.2 oz [90.0 g] |

What's in the Box

| | |
|---------------------|---|
| Included in Package | 1 - DisplayPort to DVI adapter cable – 3ft (1m) |
|---------------------|---|

****Product appearance and specifications are subject to change without notice.***