

Travel A/V adapter: 3-in-1 DisplayPort to VGA DVI or HDMI converter

Product ID: DP2VGDVHD



The DP2VGDVHD DisplayPort to VGA, DVI or HDMI converter offers a compact 3-in-1 solution for connecting your DP-equipped desktop, laptop or Ultrabook computer to a VGA, DVI, or HDMI display.

Compatible with almost any display, television or projector, this versatile converter provides the ideal plug-and-play solution for travel or BYOD (Bring Your Own Device) applications around the office. With three of the most common interfaces to choose from, the converter equips you to walk into any boardroom ready to connect to an available display device, even if you don't know what connection ports will be available.

For seamless connections from your DisplayPort-equipped computer, the converter supports video resolutions up to 1920x1200/1080p, so you can convert a DisplayPort video source to VGA, HDMI, or DVI without sacrificing video quality.

The DisplayPort converter offers a small footprint and lightweight design that makes it easy to keep on hand without it taking up too much space in your laptop bag.

The DP2VGDVHD is backed by a 3-year StarTech.com warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Keep the adapter with you while traveling, to connect to virtually any display
- Connect your BYOD laptop/Ultrabook to a provided HDMI, DVI, or VGA display at work

- Connect a DVI, VGA, or HDMI display to your DisplayPort computer, to use as a secondary monitor

Features

- Three-in-one adapter - DP to: VGA, DVI, HDMI
- Support for video resolution up to 1920x1200/1080p
- Plug-and-play installation
- Small footprint
- Portable, lightweight construction

Hardware	Warranty	3 Years
	Active or Passive Adapter	Active
	Active or Passive Adapter	Passive
	AV Input	DisplayPort - 1.2
	AV Output	DVI-D - Single-Link
	AV Output	HDMI - 1.4
	AV Output	VGA
	Audio	Yes
Performance	Maximum Cable Distance To Display	49.9 ft [15.2 m] 1920x1200/1080p
	Maximum Analog Resolutions	1920x1200/1080p
	Maximum Digital Resolutions	Yes
	Wide Screen Supported	DVI - No Audio Support
	Audio Specifications	HDMI - 7.1 Channel Audio
	Audio Specifications	VGA - No Audio Support
	Audio Specifications	
Connector(s)	Connector A	DisplayPort (20 pin)
	Connector B	DVI-D (25 pin)
	Connector B	VGA (15 pin, High Density D-Sub)
	Connector B	HDMI (19 pin)
Special Notes / Requirements	Note	Only one video output is supported on the video adapter at a time. If multiple connections are made, only one of the outputs will function.
	Note	The HDMI port is a passive port.
	Note	The DVI-D is a passive port.

The VGA port is an active port.

Maximum Cable Distance to Display refers to digital video. VGA distance capabilities are dependent upon the quality of your cabling

Environmental	Operating Temperature	0C to 45C (32F to 113F)
	Storage Temperature	-10C to 80C (14F to 176F)
	Humidity	10%-85%RH
Physical Characteristics	Color	Black
	Cable Length	5.9 in [1.5 cm]
	Product Length	10.5 in [2.7 cm]
	Product Width	1.8 in [45.000 mm]
	Product Height	0.8 in [20.000 mm]
	Weight of Product	2.3 oz [65.000 g]
Packaging Information	Package Length	8.7 in [2.2 cm]
	Package Width	7.9 in [2.0 cm]
	Package Height	0.0 in [0.100 mm]
	Shipping (Package) Weight	2.6 oz [73.000 g]
What's in the Box	Included in Package	DisplayPort to HDMI/VGA/DVI Adapter
	Included in Package	Installation Guide

****Product appearance and specifications are subject to change without notice.***

