

10m DVI-D Dual Link Cable – M/M

**Product ID:** DVIDDMM10M



The DVIDDMM10M 10m DVI-D Dual Link cable features 2 male DVI (25-pin) connectors and offers 10 meters in cable length, making it perfect for longer connections between your desktop or laptop computer and a DVI-D monitor or projector.

The 10m DVI-D digital monitor cable supports resolutions of up to 2560x1600 and transmission rates of up to 9.9 Gbits/sec and is fully compliant with DVI DDWG standards.

Designed and constructed for maximum durability, this high quality digital video cable is backed by StarTech.com's Lifetime Warranty.

## Certifications, Reports and Compatibility

## Applications

- Connect your desktop or laptop computer to a DVI-D Dual Link display or projector

## Features

- Supports a maximum resolution of 2560x1600
- High-speed digital transmission rate of up to 9.9 Gbits/sec
- Ferrite core eliminates EMI interference
- Compliant with DVI DDWG Standards
- Aluminum-Mylar Foil with Braided Shielding

- Supports hot-plugging of DVI display devices

---

#### Hardware

Warranty	Lifetime
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid
Fire Rating	CMG Rated (General Purpose)
Number of Ferrites	2
Industry Standards	DVI DDWG Standard

---

#### Connector(s)

Connector A	DVI-D (25 pin)
Connector B	DVI-D (25 pin)

---

#### Physical Characteristics

Color	Black
Connector Style	Straight
Wire Gauge	28 AWG
Cable Length	32.8 ft [10 m]
Cable OD	0.3 in [8.6 mm]
Product Length	32.8 ft [10 m]
Weight of Product	32.5 oz [920 g]

---

#### Packaging Information

Package Quantity	1
Package Length	13.0 in [33 cm]
Package Width	10.0 in [25.5 cm]
Package Height	2.8 in [72 mm]



Shipping (Package) Weight	33.2 oz [940 g]
------------------------------	-----------------

---

**What's in the  
Box**

Included in Package	10m DVI-D Dual Link Digital Video Monitor Cable - M/M
---------------------	---

---

***\*Product appearance and specifications are subject to change without notice.***

