

3m DVI-D Dual Link Cable – M/M

Product ID: DVIDDMM3M



The DVIDDMM3M 3m DVI-D Dual Link cable features 2 male DVI (25-pin) connectors and provides a reliable, purely digital connection between your desktop or laptop computer and a DVI-D monitor or projector.

The 3m DVI-D digital monitor cable supports resolutions of up to 2560x1600 and transmission rates of up to 9.9 Gbits/sec and is fully compliant with DVI DDWG standards.

Designed and constructed for maximum durability, this high quality digital video cable is backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility

Applications

- Connect your desktop or laptop computer to a DVI-D Dual Link display or projector

Features

- Supports a maximum resolution of 2560x1600
- High-speed digital transmission rate of up to 9.9 Gbits/sec
- Ferrite core eliminates EMI interference
- Compliant with DVI DDWG Standards
- Aluminum-Mylar Foil with Braided Shielding

- Supports hot-plugging of DVI display devices

Hardware

Warranty	Lifetime
Number of Conductors	24
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid
Fire Rating	CMG Rated (General Purpose)
Number of Ferrites	2
Industry Standards	DVI DDWG Standard

Connector(s)

Connector A	DVI-D (25 pin)
Connector B	DVI-D (25 pin)

Physical Characteristics

Color	Black
Connector Style	Straight
Wire Gauge	28 AWG
Cable Length	9.8 ft [3 m]
Cable OD	0.3 in [8.6 mm]
Product Length	9.8 ft [3.0 m]
Product Width	1.6 in [39.6 mm]
Product Height	0.6 in [16 mm]
Weight of Product	13.6 oz [384.0 g]

Packaging Information

Package Quantity	1
------------------	---



Package Length	15.4 in [39.0 cm]
Package Width	5.3 in [13.5 cm]
Package Height	0.0 in [0.1 mm]
Shipping (Package) Weight	13.9 oz [394.0 g]

What's in the Box

Included in Package	3m DVI-D Dual Link Digital Video Monitor Cable - M/M
---------------------	--

****Product appearance and specifications are subject to change without notice.***

