

4 Port ExpressCard RS232 Serial Card Adapter with 16950 UART

Product ID: EC4S950



This 4 Port ExpressCard Serial Adapter Card lets you add four RS232 serial ports to your laptop or ExpressCard equipped desktop computer, using an available ExpressCard slot.

Featuring 128-byte FIFO communication, and a high performance 16C950 UART, the ExpressCard Serial Adapter card offers up to 921.6Kbps data transfer rates, which ensures peak communication with your serial peripheral devices.

Certifications, Reports and Compatibility

Applications

- Works with serial modems, POS devices, PDAs, digital cameras, printers, ISDN terminal adapters, and more.

Features

- 128-byte deep FIFO data buffer
- Automated in-band flow control
- Offers 4 DB9 RS-232 ports to connect a serial device to a notebook with an available ExpressCard slot
- Automated in-band software flow control using programmable Xon/Xoff in both directions

Hardware

Warranty

Lifetime

Ports	4
Interface	Serial
Bus Type	ExpressCard
Card Type	34mm ExpressCard
Port Style	External Hub
Chipset ID	PLX/Oxford - OXuPCI954

Performance

Serial Protocol	RS-232
Max Baud Rate	921.6 Kbps
FIFO	128 Bytes

Connector(s)

Connector Type(s)	ExpressCard (34mm)
External Ports	DB-9 (9 pin, D-Sub)

Software

OS Compatibility	Windows 2000, XP, Vista, 7, 8 Windows Server 2003 Linux 3.5 to 4.4.x <i>LTS Versions only</i>
------------------	---

Environmental

Operating Temperature	0C to 55C (32F to 131F)
Storage Temperature	-20C to 85C (-4F to 185F)
Humidity	5~95% RH

Packaging Information

Package Length	9.1 in [23 cm]
Package Width	6.5 in [16.5 cm]
Package Height	1.7 in [42 mm]
Shipping (Package) Weight	12.7 oz [360 g]



What's in the Box

Included in Package	EXPRESS CARD
	4 PORT DB9 EXPANSION PORT
	DRIVER CD
	INSTRUCTION MANUAL

****Product appearance and specifications are subject to change without notice.***

