

## 10m Fiber Optic Cable - Multimode Duplex 62.5/125 LSZH Fiber Jumper Cord - LC/LC

Produkt-ID: FIBLCLC10



The FIBLCLC10 10-meter (32.8ft) Multimode 62.5/125 Duplex Fiber Patch Cable is terminated at both ends with LC (male) connectors, to provide the necessary connection between fiber networking devices for high-speed, long distance networks.

This LC-LC patch cable is housed in a LSZH (Low-Smoke, Zero-Halogen) flame retardant jacket, to ensure minimal smoke, toxicity and corrosion when exposed to high sources of heat, in the event of a fire. Making it ideal for use in industrial settings, central offices and schools, as well as residential settings where building codes are a consideration.

To ensure optimum performance, our multimode fiber duplex cable is individually tested and certified to be within acceptable optical insertion loss limits for guaranteed compatibility and 100% reliability.

Backed by Lifetime Warranty, our LC-LC Multimode Fiber Patch cable is guaranteed to provide long-lasting dependability, and top quality performance.

### Zertifikate Berichte und Kompatibilität



### Anwendungen

- Used by long distance networks with mission critical data
- Telecommunication/Data communication

- Broadband systems
- Ideal solution for data applications requiring high speed data transmission

## Merkmale

- Attenuation loss meets or exceeds industry standards
- LSZH (Low-Smoke, Zero-Halogen) cable jacket
- Immune to electrical interference

---

### Hardware

|                           |                                        |
|---------------------------|----------------------------------------|
| Garantiebestimmungen      | Lifetime                               |
| Faseroptikgröße           | 62.5/125                               |
| Feuerwiderstandssklasse   | LSZH-bewertet (Low Smoke Zero Halogen) |
| Faseroptikklassifizierung | OM1                                    |

---

### Leistung

|                            |                |
|----------------------------|----------------|
| Max. Datenübertragungsrate | 10 Gbit/s      |
| Kabelnennwerte             | 1Gbps / 10Gbps |
| Faseroptiktyp              | Multimodus     |

---

### Steckverbinder

|                  |                   |
|------------------|-------------------|
| Steckverbinder A | 1 - Faseroptik LC |
| Steckverbinder B | 1 - Faseroptik LC |

---

### Umgebungsbedingungen

|                    |                                      |
|--------------------|--------------------------------------|
| Betriebstemperatur | -20°C to 60°C (-4°F to 140°F)        |
| Lagertemperatur    | -20°C to 60°C (-4°F to 140°F)        |
| Feuchtigkeit       | 0 bis 90 % relative Luftfeuchtigkeit |

---

Physische  
Eigenschaften

|                |                  |
|----------------|------------------|
| Farbe          | Orange           |
| Kabellänge     | 32.8 ft [10 m]   |
| Produktlänge   | 32.8 ft [10.0 m] |
| Produktbreite  | 0.0 in [0.0 cm]  |
| Produkthöhe    | 0.0 in [0.0 cm]  |
| Produktgewicht | 4.7 oz [134.0 g] |

Verpackungsinform  
ationen

|                                |                  |
|--------------------------------|------------------|
| Paketmenge                     | 1                |
| Paketlänge                     | 6.6 in [16.8 cm] |
| Paketbreite                    | 7.8 in [19.8 cm] |
| Pakethöhe                      | 1.4 in [3.5 cm]  |
| Versandgewicht<br>(Verpackung) | 5.2 oz [146.0 g] |

Garantieinformatio  
nen

|          |          |
|----------|----------|
| Warranty | Lifetime |
|----------|----------|

\* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.