

40 ft DVI-D Dual Link Cable - M/M

Productcode: DVIDDMM40



The DVIDDMM40 40ft DVI-D Dual Link cable features 2 male DVI (25-pin) connectors and offers 40 feet in cable length, making it perfect for longer connections between your desktop or laptop computer and a DVI-D monitor or projector.

The 40 ft DVI-D digital monitor cable supports resolutions of up to 2560x1600 and transmission rates of up to 9.9 Gbits/sec and is fully compliant with DVI DDWG standards.

Designed and constructed for maximum durability, this high quality digital video cable is backed by StarTech.com's Lifetime Warranty.

Certificaties, rapporten en compatibiliteit



Toepassingen

- Compatibel met LCD-schermen, CRT-schermen, projectoren en HDTV

Eigenschappen

- Supports a maximum resolution of 2560x1600
- High-speed digital transmission rate of up to 9.9 Gbits/sec

- Ferrite core eliminates EMI interference
- Aluminum-Mylar folie met gevlochten afscherming
- Ondersteunt hot-plugging van DVI-beeldschermen
- Voldoet aan de DVI DDWG-specificaties

Hardware

Garantiebeleid	Lifetime
Connectormateriaal	Nikkel
Industriestandaarden	DVI DDWG Standard

Connector(en)

Connector A	1 - DVI-D (25-polig)
Connector B	1 - DVI-D (25-polig)

Gebruiksomgeving

Bedrijfstemperatuur	0°C to 50°C (32°F to 122°F)
Opslagtemperatuur	-20 to 70°C (-4°F to 158°F)
Vochtigheid	0 tot 95%

Fysieke eigenschappen

Kleur	Zwart
Draaddikte	28 AWG
Kabellengte	40.0 ft [12.2 m]
Lengte product	40.0 ft [12.2 m]
Breedte product	0.0 in [0.0 mm]
Hoogte product	0.0 in [0.0 mm]
Gewicht product	2.5 lb [1.1 kg]

Verpakkingsinformatie

Verpakkingsaantal	1
Lengte Verpakking	8.7 in [22.0 cm]
Package Width	8.7 in [22.0 cm]
Package Height	2.4 in [6.0 cm]
Verzendgewicht (verpakt)	2.5 lb [1.1 kg]

Wat wordt er
meegeleverd

Meegeleverd	1 - 40 ft DVI-D Dual Link Cable - M/M
-------------	---------------------------------------

Garantiebepalinge
n

Warranty	Levenslang
----------	------------

* Uitvoering en specificaties van het product zijn zonder aankondiging vatbaar voor wijzigingen.