

10 ft DVI-D Single Link Monitor Extension Cable - M/F

Product ID: DVIDSMF10



The DVIDSMF10 DVI-D Single-Link Monitor Extension Cable allows you to extend the connection between your desktop workstation and DVI monitor, or your laptop and projector by up to 10-feet.

The single-link cable supports resolutions of up to 1920x1200 and transmission rates of up to 4.95 Gbits/sec, and is fully compliant with DVI DDWG standards.

This durable DVI male to female cable is designed to provide a high quality digital video experience, and is backed by StarTech.com's lifetime warranty.

Certifications, Reports and Compatibility

Applications

- Extend the connection distance between your desktop or laptop computer and a DVI-D Single Link display or projector by up to 10ft

Features

- Supports a maximum resolution of 1920x1200
- Supports hot plugging of DVI display devices
- Compliant with DVI DDWG Standards
- High-speed digital transmission rate of up to 4.95 Gbits/sec
- Aluminum-Mylar Foil with Braided Shielding

- Molded connectors with strain relief

Hardware

Warranty	Lifetime
Industry Standards	DVI DDWG Standard

Connector(s)

Connector A	DVI-D (19 pin)
Connector B	DVI-D (25 pin)

Physical Characteristics

Color	Black
Wire Gauge	28 AWG
Cable Length	10.0 ft [3.0 m]
Product Length	10.0 ft [3.0 m]
Weight of Product	9.4 oz [266 g]

Packaging Information

Package Length	8.7 in [22 cm]
Package Width	7.9 in [20 cm]
Package Height	1.4 in [35 mm]
Shipping (Package) Weight	9.7 oz [275 g]

What's in the Box

Included in Package	10 ft DVI-D Single Link Monitor Extension Cable - M/F
---------------------	---

****Product appearance and specifications are subject to change without notice.***

