

10 ft DVI-D Single Link Monitor Extension Cable - M/F

Product ID: DVIDSMF10



The DVIDSMF10 DVI-D Single-Link Monitor Extension Cable allows you to extend the connection between your desktop workstation and DVI monitor, or your laptop and projector by up to 10-feet.

The single-link cable supports resolutions of up to 1920x1200 and transmission rates of up to 4.95 Gbits/sec, and is fully compliant with DVI DDWG standards.

This durable DVI male to female cable is designed to provide a high quality digital video experience, and is backed by StarTech.com's lifetime warranty.

Certifications, Reports and Compatibility



Applications

- Extend the connection distance between your desktop or laptop computer and a DVI-D Single Link display or projector by up to 10ft

Features

- Supports a maximum resolution of 1920x1200
- High-speed digital transmission rate of up to 4.95 Gbits/sec
- Aluminum-Mylar Foil with Braided Shielding

- Supports hot plugging of DVI display devices
- Compliant with DVI DDWG Standards
- Molded connectors with strain relief

Hardware

| | |
|--------------------|-------------------|
| Warranty | Lifetime |
| Industry Standards | DVI DDWG Standard |

Connector(s)

| | |
|-------------|--------------------|
| Connector A | 1 - DVI-D (19 pin) |
| Connector B | 1 - DVI-D (25 pin) |

Physical Characteristics

| | |
|-------------------|-----------------|
| Color | Black |
| Wire Gauge | 28 AWG |
| Cable Length | 10.0 ft [3.0 m] |
| Product Length | 10.0 ft [3.0 m] |
| Weight of Product | 9.4 oz [266 g] |

Packaging Information

| | |
|---------------------------|------------------|
| Package Quantity | 1 |
| Package Length | 6.9 in [17.6 cm] |
| Package Width | 7.7 in [19.5 cm] |
| Package Height | 1.7 in [4.2 cm] |
| Shipping (Package) Weight | 9.8 oz [278.0 g] |

What's in the Box

| | |
|---------------------|---|
| Included in Package | 10 ft DVI-D Single Link Monitor Extension Cable - M/F |
|---------------------|---|

**Product appearance and specifications are subject to change without notice.*