

Multi-Input to HDMI Automatic Switch and Converter - 4K - TAA

Product ID: HDVGADP2HD



This multi-input converter switch lets you connect your DisplayPort (DP), HDMI and VGA audio/video sources to one HDMI display or projector. The switch enables you to automatically or manually switch between your video sources and features built-in signal conversion, which eliminates the cost and hassle of using additional adapters for the sake of compatibility.

This versatile A/V switch supports video resolutions up to 1920x1200 (1080p) on your VGA source and up to 4K at 30 Hz on your DisplayPort and HDMI video sources. For a tidy, professional installation, the converter switch includes mounting hardware.

The A/V switch features built-in HDMI conversion, so you can connect two HDMI sources as well as a VGA and a DisplayPort video source to the same HDMI display, without having to use additional adapters or scalars.

The converter switch ensures hassle-free operation, with two different auto-switching modes: auto-detect switching, which detects and selects a newly connected device, or priority selection, which lets you choose which port should be activated by default for automatic switching. The converter switch is perfect for digital signage applications where an automatic switch can replace a failed source with a secondary input to avoid embarrassing video outages.

This versatile A/V switch has been designed with the boardroom and classroom in mind, with HDMI, VGA and DisplayPort inputs to support a wide range of devices, and a built-in converter that makes it easy to connect to the room's display without having to connect additional adapters. Plus, automatic switching encourages on-the-fly collaboration among students or co-workers, by making it so easy to share a projector or other display device between multiple sources.

The video switch maintains Ultra HD 4K picture quality while switching between content from HDMI and DisplayPort source devices, including Blu-ray players and DVD players, computer systems, video game consoles, digital cable and satellite boxes and A/V receivers.

4K video support ensures a higher level of image clarity and visibility, delivering four times the resolution of 1080p -- 8.29 million pixels versus 2.07 million pixels. It offers a more engaging visual experience for audiences in a wide range of venues, including conference centers, boardrooms, educational facilities, and commercial settings.

When connecting a VGA source, the switch supports high-definition resolutions up to 1920 x 1200. With its

exceptional resolution and image quality, this switch is ideal for bringing your digital signage to life.

The HDVGADP2HD is TAA compliant and backed by a 2-year StarTech.com warranty and free lifetime support.

Certifications, Reports and Compatibility



Applications

- Use in your classroom or boardroom display, to enable presenters to connect a wide range of devices
- Automatically switch between your set-top box or computer, in a home theatre environment
- Connect and switch between DP, VGA and HDMI video sources on a test bench, for troubleshooting different types of computers

Features

- Save the hassle and expense of using additional adapters, with a switch that accommodates VGA, DP and HDMI inputs with a single HDMI output
- Effortless control with auto-detect and priority port selection
- Astonishing picture quality with support for resolutions up to 4K at 30Hz
- Backward compatible with high-definition resolutions up to 1920 x 1200 or 1080p
- Mounting hardware included

Hardware

Warranty	2 Years
Active or Passive Adapter	Active
AV Input	HDMI
	VGA
	DisplayPort
Ports	4
AV Output	HDMI

	Audio	Yes
Performance		
	Maximum Analog Resolutions	1920 x 1200 at 60 Hz
	Maximum Digital Resolutions	3840x2160 at 30 Hz
	Supported Resolutions	HDMI and DisplayPort 1024x768 1280x720 (High-definition 720p) 1920x1080 (High-definition 1080p) 1920x1200 2560x1440 2560x1600 3840x2160 (Ultra HD 4K) VGA 1024 x 768 1280 x 720 (High-definition 720p) 1920 x 1080 (High-definition 1080p) 1920 x 1200
	Wide Screen Supported	Yes
	Audio Specifications	2-channel 3.5mm stereo audio (VGA) 2-channel DisplayPort stereo audio (DP) 7.1 surround sound (HDMI)
Connector(s)		
	Connector A	2 - HDMI (19 pin) 1 - VGA (15 pin, High Density D-Sub) 1 - DisplayPort (20 pin) 1 - 3.5 mm Mini-Jack (3 Position)

		1 - Infrared
	Connector B	1 - HDMI (19 pin)
Indicators		
	LED Indicators	4 - selected port LEDs
		1 - status LED
Power		
	Power Source	AC Adapter Included
	Input Voltage	100 - 240 AC
	Output Voltage	12V DC
	Output Current	1.5 A
	Center Tip Polarity	Positive
	Plug Type	M
	Power Consumption (In Watts)	18
Environmental		
	Operating Temperature	0C to 40C (32F to 104F)
	Storage Temperature	-10C to 60C (14F to 140F)
	Humidity	0% ~ 80%
Physical Characteristics		
	Color	Black
	Product Length	6.3 in [16.1 cm]
	Product Width	4.1 in [10.5 cm]
	Product Height	1.6 in [4.1 cm]
	Weight of Product	1.4 lb [0.6 kg]
Packaging Information		
	Package Quantity	1

Package Length	11.7 in [29.7 cm]
Package Width	8.5 in [21.6 cm]
Package Height	2.6 in [6.6 cm]
Shipping (Package) Weight	2.7 lb [1.2 kg]

What's in the Box

Included in Package	1 - converter switch
	1 - IR remote control
	1 - screw kit
	1 - mounting bracket kit
	1 - footpad set
	1 - RJ11-to-RS232 converter
	1 - RJ11 cable
	1 - universal power adapter (NA / EU / UK / AU)
	1 - quick start guide

****Product appearance and specifications are subject to change without notice.***