

## 3.5in Black External USB IDE Hard Drive Enclosure


**Product ID:** IDE3510U2



The IDE3510U2 USB IDE Hard Drive Enclosure provides cost-effective external storage, letting you connect a 3.5in IDE hard drive to a computer through USB 2.0 - perfect for extending the useful life of older IDE hard drives.

Compatible with USB 2.0-enabled Mac and PC computers, the hard drive enclosure features an attractive aluminum and steel chassis that provides maximum durability and heat dissipation.

### Certifications, Reports and Compatibility



### Applications

- Archive or make backups to existing data for added security
- Easy add-on storage for business or personal use
- Ideal for storing data from digital cameras, DV camcorders, MP3 files, computer games or for backing up personal and work documents
- Share important files and applications between computers

## Features

- Aluminum design cools and protects hard drive
- Plug and play for USB 2.0 - can be setup in minutes, designed for easy installation
- Compact design and light weight makes the unit extremely portable
- Data transfer at rates up to 480 Mbps
- LED indicators that continuously show the operating status of the hard drive
- PC, Mac, and Linux Compatible
- Saves time - Hot-swap capability allows you to connect and disconnect drives without having to shut down computer

---

### Hardware

|                        |                   |
|------------------------|-------------------|
| Warranty               | 2 Years           |
| Fan(s)                 | No                |
| Interface              | USB 2.0           |
| Number of Drives       | 1                 |
| Drive Size             | 3.5in             |
| Compatible Drive Types | IDE (ATA)         |
| Drive Installation     | Fixed             |
| Chipset ID             | Initio - INIC-151 |

---

### Performance

|                         |                      |
|-------------------------|----------------------|
| Type and Rate           | USB 2.0 - 480 Mbit/s |
| UASP Support            | No                   |
| Hardware Raid Supported | No                   |
| Max Drive Capacity      | 750Gb                |

---

### Connector(s)

|                  |                                    |
|------------------|------------------------------------|
| Drive Connectors | 1 - IDE (40 Pin, EIDE/PATA)        |
|                  | 1 - LP4 (4 pin; Large Drive Power) |
| Host Connectors  | 1 - USB B (4 pin)                  |

|                                 |                       |   |
|---------------------------------|-----------------------|---|
| <b>Software</b>                 | OS Compatibility      | OS independent; No software or drivers required |
|                                 |                       |   |
| <b>Indicators</b>               | LED Indicators        | 1 - Green - Power Indicator                     |
|                                 |                       | 1 - Red - Drive Activity                        |
| <b>Power</b>                    | Power Source          | AC Adapter Included                             |
|                                 | Input Voltage         | 115V AC   |
|                                 | Output Voltage        | 12V DC  |
|                                 | Output Current        | 2A  |
|                                 | Center Tip Polarity   | Positive  |
|                                 | Plug Type             | N   |
| <b>Environmental</b>            | Operating Temperature | 0C to 70C (32F to 158F)                         |
|                                 | Storage Temperature   | 10~90%RH  |
|                                 | Humidity              | -20C to 75C (-4F to 167F)                       |
| <b>Physical Characteristics</b> | Color                 | Black   |
|                                 | Material              | Aluminum and Steel                              |
|                                 | Product Length        | 8.7 in [22.2 cm]                                |
|                                 | Product Width         | 1.3 in [3.3 cm]                                 |
|                                 | Product Height        | 4.9 in [12.4 cm]                                |
|                                 | Weight of Product     | 17.6 oz [499 g]                                 |
| <b>Packaging Information</b>    | Package Length        | 9.5 in [24.1 cm]                                |
|                                 |                       |   |

|                           |                  |
|---------------------------|------------------|
| Package Width             | 4.0 in [10.2 cm] |
| Package Height            | 5.2 in [13.2 cm] |
| Shipping (Package) Weight | 2.2 lb [1 kg]    |

---

#### What's in the Box

|                     |   |
|---------------------|---|
| Included in Package | 1 - 3.5" USB 2.0 IDE Hard Drive Enclosure |
|                     | 1 - Black Enclosure Stand                 |
|                     | 1 - USB 2.0 Cable                         |
|                     | 1 - Power Adapter                         |
|                     | 1 - Instruction Manual                    |

---

#### Warranty Information

|          |         |
|----------|---------|
| Warranty | 2 Years |
|----------|---------|

---

***\*Product appearance and specifications are subject to change without notice.***