

Industrial Fiber to Ethernet Media Converter - 100Mbps SFP to RJ45/Cat6 - Singlemode/Multimode
Optical Fiber to Copper Network - 12-56V DC - IP-30/ -40 to +75C

Product ID: IMC100MSFP



An industrial media converter that converts fiber to copper at a network endpoint.

This media converter features an open SFP slot for any standard SFP to be used for the incoming fiber connection and is easily deployed across applications or fiber cable types. Accepts terminal block power or coaxial power connectors with the barrel plug adapter, allowing the product to be hardwired or powered using an external power supply (not included), which does not require professional installation. It can be powered using 18V-36V AC or 12V -56V DC for a high degree of flexibility including applications like solar, automotive, and rail. Includes hardware for DIN rail or wall mounting.

Designed with IP-30 housing and has an MBTF of >500,000 hrs (Telcordia/Bellcore) at 50C and an operating temperature range of include -40 C to 75 C for durability; it's rated to various vibration, shock, and free-fall standards:

- Vibration: EN 60068-2-6
- Shock: EN 60068-2-27
- Free-Fall: EN 60068-2-32

Accepts terminal block power or coaxial power connectors with the barrel plug adapter, allowing the product to be hardwired or powered using an external power supply (not included), which does not require professional installation.

The IMC100MSFP is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

Features

- **COMPACT SIZE + FLEXIBLE POWER INPUT:** Smallest form factor Fiber to Ethernet media converter - extends & converts 100Mbps fiber to RJ45 copper; powered by 18-36V AC or 12V-56V DC for solar, auto & rail
- **ROBUST DESIGN:** Industrial Network Media Converter w/MTBF 500,000+hrs @ 50C Vibration, shock & freefall rated Rugged IP-30 aluminum housing Hardened operating temp -40C to 75C
- **OPEN SFP SLOT:** Compatible with any standard SFP and can be used for multimode or single mode fiber connections; easy deployment across applications, fiber distances or fiber cable types
- **TECH SPECS:** 100Mbps AC (18-36V) or DC (12-56V) Single Mode SMF & Multi-Mode MMF Fiber 16K Jumbo Frames LFP DIN/Wall Mountable Terminal Block and/or Barrel Adapter for power flexibility
- **STARTECH.COM ADVANTAGE:** IT professionals' choice for over 30 years This media converter is backed for 2-years by StarTech.com, including free 24/5 North America based multi-lingual tech support

Hardware

Warranty	2 Years
PoE	No
Industry Standards	IEEE 802.3 10BASE-T, IEEE 802.3u 100BASE-FX, IEEE 802.3u 100BASE-TX, IEEE 802.3x
Chipset ID	IC Plus IP113B

Performance

Max Transfer Distance	100 m (328 ft)
Type	Single Mode / Multi Mode
Flow Control	IEEE 802.3x Flow Control and Back Pressure
Compatible Networks	10/100 Mbps
Auto MDIX	Yes
Jumbo Frame Support	No
General Specifications	ESD Standard: IEC 61000-4-2: Contact: 6KV; Air: 8KV, EFT Standard: IEC 61000-4-4: Power: 2KV; Signal: 2KV, Surge Standard: IEC 61000-4-5: Power: 2KV; Signal: 2KV, Vibration Standard: EN 60068-2-6, Shock Standard: EN 60068-2-27, Free-Fall Standard: EN 60068-2-32, Housing Standard: IP-30, Safety Standard: EN60950-1
MTBF	534,482 hours

Connector(s)

Connector A	RJ-45
	SFP Slot

Indicators

LED Indicators	SFP LNK/Act
	Power
	RJ45 LNK/Act
	RJ45 Link Speed

Power

Plug Type	N
Power Consumption (In Watts)	1.92W

Environmental

Operating Temperature	-40C to 75C
Storage Temperature	-40C to 85C
Humidity	5 to 95% (non-condensing)

Physical Characteristics

Color	Black
Material	Aluminum
Product Length	2.3 in [59.0 mm]
Product Width	1.4 in [36.0 mm]
Product Height	2.0 in [50.0 mm]
Weight of Product	2.9 oz [81.4 g]

Packaging Information

Package Length	4.1 in [10.5 cm]
Package Width	6.1 in [15.5 cm]
Package Height	2.5 in [64.0 mm]



Shipping (Package) Weight	8.6 oz [242.4 g]
------------------------------	------------------

What's in the Box

Included in Package	Media Converter
	Terminal Block
	Terminal Block to Barrel Power Connector Adapter
	Mounting Hardware Kit
	Quick-Start Guide

****Product appearance and specifications are subject to change without notice.***

