

4-Port Serial to Ethernet Adapter, IP Serial Device Server For Remote RS232 Devices, Wall/DIN Rail Mountable, Metal Housing, RJ45 LAN to DB9 Serial Converter, TAA

Product ID: I43-SERIAL-ETHERNET



This 4-port serial to IP converter is an efficient solution for remotely connecting and controlling a variety of RS232 serial devices over an IP-based network.

The DB9 to Ethernet Adapter family shares the same Windows Virtual COM Port software and Web User Interface (WebUI) for a unified experience. Users can employ the Windows software to view and manage all device servers within a network and to set up virtual COM ports. Alternatively, the WebUI provides a platform-independent method, allowing users to access and configure these device servers from any operating system. This flexibility ensures that administrators can manage their network of device servers efficiently, regardless of the operating system they are using.

The product family includes the following options:

- 1-Port Serial to Ethernet Adapter with PoE (I13P-SERIAL-ETHERNET)
- 1-Port Serial to Ethernet Adapter (I13-SERIAL-ETHERNET)
- 2-Port Serial to Ethernet Adapter (I23-SERIAL-ETHERNET)
- 4-Port Serial to Ethernet Adapter (I43-SERIAL-ETHERNET)

Dual power options, DC jack and terminal block, provide installation flexibility and convenience. The converter is housed in a full metal enclosure for durability in harsh environments. The DB9 over IP converter includes all necessary wall and DIN rail mounting hardware. Multiple mounting holes along the chassis allow it to be installed in the most useful orientation for any application. Dimensions of 7x2.3x0.9in (178x59.4x23mm).

The TAA-compliant IP-to-serial converter features a single RJ45 10/100 Mbps Ethernet port and supports Telnet Server (RFC2217), TCP Server, TCP Client, and UDP protocols for versatile network connectivity. It also includes a universal power adapter, supports ESD level 4 surge protection, and can supply 5VDC over pin 9 if required.

Certifications, Reports and Compatibility



Applications

Features

- **FOUR PORT SERIAL TO IP CONVERTER:** Connect different RS232 serial devices remotely over an IP-based network; Use for POS systems, barcode readers, sensors, weighing systems, CNC controllers & PLCs; DB9 serial port supports up to 921.6Kbps; TAA Compliant
- **UNIFIED ECOSYSTEM EXPERIENCE:** All our device servers share the same management software and Web UI; View/manage individual devices with a common UI on any OS; Windows software to set up virtual com ports and view/manage all device servers on the network
- **VERSATILE CONFIGURATIONS:** RJ45 LAN to RS232 converter support TCP client/server mode to enable serial tunneling between two device servers over a LAN; Export/import settings, custom naming / location, admin password protection, and upgradeable firmware
- **ETHERNET AND POWER OPTIONS:** Single 10/100Mbps RJ45 port w/auto-negotiation; Serial device server operates over Telnet (RFC2217)/UDP/TCP; Serial to LAN converter includes a power adapter & supports 5V over pin 9 for serial devices
- **RUGGED AND MOUNTABLE ENCLOSURE:** All-metal housing ensures durability in harsh conditions; Supports Level-4 ESD protection (15kV air/8kV contact); Includes the necessary wall and DIN rail mounting hardware; Dimensions 7x2.3x0.9in (178x59.4x23mm);
- **SERIAL TO IP CONVERTER OPTIONS:** Our family of device servers includes the following options: I13-SERIAL-ETHERNET (1 Port), I13P-SERIAL-ETHERNET (1 Port w/ PoE), I23-SERIAL-ETHERNET (2 Port), and I43-SERIAL-ETHERNET (4 Port)

Hardware

Warranty	2 Years
Ports	4
Interface	Serial
Industry Standards	IEEE 802.3u (100BASE-TX) , IEEE 802.3i (10BASE-TX) , EIA/TIA-232

Performance

Serial Protocol	RS-232
-----------------	--------

Max Baud Rate	921.6 Kbps
Data Bits	7, 8
Flow Control	RTS/CTS , X-ON/X-OFF, None
Parity	None, Even, Odd, Mark, Space
Stop Bits	1, 2
Remote Management Ability	Yes
Surge Protection	ESD (Electrostatic Discharge) Level 4 Protection: 15kV IEC1000-4-2 Air 8kV IEC1000-4-2 Contact
Compatible Networks	10/100 Mbps
Auto MDIX	Yes
Full Duplex Support	Yes
Supported Protocols	IP, Telnet RFC2217, TCP Server, TCP Client, and UDP

Connector(s)

Connector Type(s)	4 - DB-9 (9 pin, D-Sub) 1 - RJ-45 1 - Terminal Block (2 Wire)
Connector A	1 - RJ-45
Connector B	4 - DB 9-pin Serial

Software

OS Compatibility	 Virtual COM software supports Windows only. Compatible with Windows 8, 8.1, 10, 11
------------------	---

Special Notes / Requirements

Note	 Note: The device server's hardware is compatible with macOS and Linux; however, the provided Virtual
------	--

COM software is not compatible with these operating systems.
When used with macOS and Linux, the device server can only be configured using the WebUI.

Indicators

LED Indicators	<p>1 - RJ-45 Right LED Steady green: Ethernet connection Blinking green: Activity Off: Ethernet is not connected</p> <p>8 - DB-9 Left LED Blinking green: Receive data activity Off: No activity Right LED Blinking green: Transmit data activity Off: No activity</p> <p>1 - Power LED Steady green: Power is on Off: Power is off Blinking green: Restoring to factory settings</p>
----------------	---

Power

Power Source	AC Adapter Included
Input Voltage	100 - 240 AC
Input Current	0.48A
Output Voltage	5V DC
Output Current	3A
Center Tip Polarity	Positive
Plug Type	M
Power Consumption (In Watts)	15W

Environmental

Operating Temperature	0C to 60C (32F to 140F)
Storage Temperature	-20C to 75C (-4F to 167F)
Humidity	5~95% RH (Non-condensing)

Physical Characteristics

Color	Black
Material	Steel
Product Length	2.4 in [6.0 cm]
Product Width	7.0 in [17.9 cm]

Product Height	0.9 in [2.3 cm]
Weight of Product	14.1 oz [400.0 g]

Packaging Information

Package Length	9.5 in [24.2 cm]
Package Width	6.5 in [16.6 cm]
Package Height	2.2 in [5.5 cm]
Shipping (Package) Weight	1.4 lb [0.6 kg]

What's in the Box

Included in Package	1 - 4-Port Serial Over IP Device Server
	1 - Din Rail Kit
	2 - Din Rail Screws
	1 - Universal Power Adapter
	1 - Quick-Start Guide

****Product appearance and specifications are subject to change without notice.***