

## 2.5in Silver USB 2.0 to IDE External Hard Drive Enclosure

**Product ID:** IDE2510U2



This USB 2.0 to IDE 2.5 in. External Hard Drive Enclosure lets you transform virtually any 2.5in IDE notebook hard drive into the perfect portable storage solution.

Ideal for storing digital multimedia and other demanding applications, the IDE hard drive enclosure allows you to get the most out of your hard drive, connecting to a host computer using USB 2.0 (also backward compatible with USB 1.1), for maximum data transfer rates of up to 480Mbps.

A truly portable solution, the enclosure features lightweight yet durable aluminum construction, as well as a small form factor design that fits perfectly into your pocket or notebook bag when not in use. To eliminate the hassle of having to find a power outlet when you're ready to back up your data or load your stored files, the enclosure requires no external power supply, as it's powered through USB connection to the host computer.

## Certifications, Reports and Compatibility

### Applications

- Create a fast, ultra portable external storage solution for laptops or netbooks
- Add-on storage to any USB enabled computer system
- Backup data to an external storage device
- Retrieve data from old laptop drive, or turn the unused drive into additional external storage space

### Features

- Light-weight, durable aluminum construction

- High Speed USB 2.0 compliant host interface, with transfer rates up to 480 Mbps
- Power/activity LED
- Compatible with PATA (IDE) 66/100/133 Mbps drives
- Supports 2.5" form factor IDE hard drives
- Powered directly from the USB ports
- Compact, portable design
- Includes a protective carrying pouch

---

#### Hardware

Warranty	2 Years
Fan(s)	No
Interface	USB 2.0
Bus Type	USB 2.0
Number of Drives	1
Drive Size	2.5in
Compatible Drive Types	IDE (ATA)
Drive Installation	Fixed
Chipset ID	Genesys Logic - GL811E

---

#### Performance

Maximum Data Transfer Rate	480Mbps
UASP Support	No
Hardware Raid Supported	No
Max Drive Capacity	160GB @ 5400 RPM

---

#### Connector(s)

Connector Type(s)	USB Mini-B (5 pin)
-------------------	--------------------

---

#### Software



OS Compatibility	OS independent; No software or drivers required
------------------	---

---

**Indicators**

LED Indicators	Green: Power / Red: Drive Activity
----------------	------------------------------------

---

**Power**

Power Source	Not Included (not required for standard applications)
Input Voltage	5 DC

---

**Environmental**

Operating Temperature	0C to 60C (32F to 140F)
Storage Temperature	-20C to 70C (-4F to 158F)
Humidity	0~90% RH

---

**Physical Characteristics**

Color	Silver
Material	Aluminum
Max Drive Height	0.4 in [9.5 mm]
Product Length	4.7 in [12 cm]
Product Width	3.0 in [75 mm]
Product Height	0.4 in [10 mm]
Weight of Product	2.2 oz [62.1 g]

---

**Packaging Information**

Package Length	8.3 in [21 cm]
Package Width	2.0 in [50 mm]
Package Height	5.3 in [13.4 cm]
Shipping (Package) Weight	8.5 oz [240 g]

---

**What's in the Box**

Included in Package	2.5in IDE Enclosure
---------------------	---------------------



Instruction Manual

Screw Kit

Mini Screwdriver

USB 2.0 Y-Cable

Protective Case

---

***\*Product appearance and specifications are subject to change without notice.***

