

4 Bay Thunderbolt 3 NVMe Enclosure, For M.2 NVMe SSD Drives, 1x DisplayPort Video/ 2x TB3 Downstream Ports, 40Gbps, 72W Power Supply, External Hard Drive Enclosure

Product ID: M2E4BTB3



This Thunderbolt 3 to 4x M.2 PCIe SSD enclosure enables you to turn four M-Key PCI-Express based M.2 NVMe or AHCI solid state drives (SSDs) into a high-performance external storage solution.

The SSD enclosure is self-powered with an included 72W EPS power supply that powers the enclosure, the connected drives, and provides up to 15W of power to any downstream Thunderbolt 3 devices. A 2.3 ft. (70 cm) Thunderbolt 3 Certified host cable is also included, to connect the enclosure to your computer.

The enclosure is compatible with 80mm M.2 PCIe based (M-Key) single/double-sided SSDs. Create an external storage solution that utilizes the high-performance bandwidth available to your Thunderbolt 3 port, providing combined data transfer speeds of up to 40Gbps for up to four drives. The vented metal enclosure features thermal pads and a cooling fan to ensure your SSDs are operating at optimal temperatures.


A single 8 Gbps PCIe lane is dedicated to each connected drive. This ensures consistent read/write performance across the entire enclosure, regardless of individual drive activity. The enclosure also supports software RAID with storage management systems like Storage Spaces (Microsoft), RAID Assistant (macOS), or mdraid/mdadm (Linux). The support for software RAID, combined with exceptional drive performance, makes this the ideal enclosure for creative professionals working with large files such as high-resolution graphics, video, and CAD files.

This enclosure is Thunderbolt Certified to ensure an optimal user experience and compatibility when connected to a Thunderbolt 3 host device, such as a MacBook Pro 16, 13, Air, Lenovo ThinkPad X1 Carbon / T Series, Dell XPS / Latitude / Precision or HP EliteBook. The external drive enclosure is also forward compatible with Thunderbolt 4 devices (at Thunderbolt 3 performance).

The enclosure features a DisplayPort output port, enabling you to connect a DisplayPort monitor to your computer through the Thunderbolt 3 enclosure, with resolutions up to 4K 60Hz. The enclosure also features a downstream Thunderbolt 3 port for daisy chaining an additional TB3 device or connect an additional TB3 compatible display (up to 5K 60Hz).

M2E4BTB3 is backed by a 2-year StarTech.com warranty, with free lifetime North American based multilingual technical support.

Certifications, Reports and Compatibility



Applications

- Build a software RAID array with a storage management system like Storage Spaces (Microsoft), RAID Assistant (macOS), or mdraid/mdadm (Linux)
- Ideal for creative professionals working with large files such as high-resolution graphics, video, and CAD files

Features

- **HIGH PERFORMANCE M.2 STORAGE VIA THUNDERBOLT 3** : Turn up to 4 PCIe 80mm M.2 SSDs (M-Key) into an external TB3 storage solution; Data transfer speeds up to 40Gbps; Downstream TB3 port; DisplayPort video output; Vented metal enclosure w/thermal pads & fan
- **MAXIMIZE DRIVE SPEED**: Connect up to four M.2 PCIe NVMe and/or AHCI drives with an 8Gbps PCIe lane dedicated to each SSD; Supports software RAID with storage management systems like Storage Spaces (Microsoft) , RAID Assistant (macOS), mdraid/mdadm (Linux)
- **FLEXIBLE PORT OPTIONS**: DisplayPort output to connect to a display with resolutions up to 4K 60Hz; Downstream TB3 port to daisy chain additional TB3 devices or a compatible TB3 display (up to 5K 60Hz); Connected devices share bandwidth with connected SSDs
- **THUNDERBOLT 3 CERTIFIED**: Works w/TB3 & TB4 host devices like MacBook Pro 16/13/Air (Dual displays on Apple M1/M2/M3 Pro/Max Processors; Only single display on M1/M2/M3), Lenovo ThinkPad X1 Carbon/T Series, Dell XPS/Latitude/Precision & HP EliteBook
- **POWER ADAPTER & THUNDERBOLT 3 CABLE INCLUDED**: Self powered with an included 72W EPS power supply that powers the enclosure, the connected drives and provides 15W to TB3 port; Includes 2.3 ft (70cm) TB3 certified passive cable; NOT COMPATIBLE WITH SATA SSD

Hardware

Warranty	2 Years
Fan(s)	Yes
Fans	1 - 40 mm

Interface	Thunderbolt 3
Bus Type	Thunderbolt 3
Number of Drives	4
Drive Size	80 mm - M.2 PCIe
Compatible Drive Types	M.2 (PCIe, NVMe, M-Key, NGFF) M.2 (PCIe, AHCI, M-Key, NGFF)
Drive Installation	Fixed
Supported Drive Height(s)	2280
Fan Bearing Type	Sleeve Bearing
Chipset ID	Intel - JHL6540 TI - TPS65983B

Performance

Noise Level	34.5dB @ 50cm
Maximum Data Transfer Rate	40 Gbps
Type and Rate	Thunderbolt 3 - 40 Gbit/s
TRIM Support	Yes
4Kn Support	Yes
S.M.A.R.T. Support	Yes
Type and Rate	NVMe (PCIe x1 Gen 3; 8Gbps)
MTBF	50,000 Hours

Connector(s)

Drive Connectors	4 - M.2 (PCIe, M-Key, AHCI/NVMe, NGFF)
Host Connectors	1 - Thunderbolt 3 USB-C (24-pin) (40Gbps)
Other Interface(s)	1 - Thunderbolt 3 USB-C (24-pin) (40Gbps) 1 - 20 pin DisplayPort Female

Software		
	OS Compatibility	OS Independent; No Software or Drivers Required
Special Notes / Requirements		
	Note	<p>Displays Supported: 2</p> <p>Maximum Digital Resolutions:</p> <p>Thunderbolt 3 - 5120 x 2880 at 60Hz</p> <p>DisplayPort - 4086x2160 at 60Hz</p> <ul style="list-style-type: none"> - This M.2 enclosure does not provide full power delivery but will provide 15W of power, resulting in a slow charge to some laptops, such as MacBook Pro. When the dock is connected to your host laptop, a charging icon may appear on the screen. This is only sufficient to charge your laptop in sleep state, and charging will require an extended time period. - 5K support can only be achieved using a Thunderbolt 3 5K monitor. DisplayPort 5K monitors will not work at 5K with this M.2 enclosure - A 4K-capable display is required to achieve 4K resolution (4K is also known as 4K x 2K). - Certain monitors may be limited to 4K at 30Hz when connecting through DisplayPort. These monitors include the following models: Dell P2715Q, Viewsonic VX2475Smhl-4K, Philips 288P6LJEB, LG 31MU97C-B, and Asus PB287Q (these models must be set to 4K at 30Hz). - When connecting a display to one of the Thunderbolt 3 USB-C ports, a USB-C video adapter may be required, depending on the input of your display. - Secondary Thunderbolt 3 port can also be used to connect USB 3.2 Gen 2 (10 Gbps) USB-Type C devices, such as USB 3.2 Gen 2 Hubs. Backwards compatible with USB 3.2 Gen 1 (5 Gbps), and USB 2.0. - Not Compatible with SATA Based M.2 Drives.
Indicators		
	LED Indicators	<p>1 - Power (Illuminates when powered on)</p> <p>4 - Drive Activity (Flashes when drive activity is detected)</p>
Power		
	Power Source	AC Adapter Included
	Input Voltage	110V-240V AC

Input Current	2 A
Output Voltage	12V DC
Output Current	6 A
Center Tip Polarity	Positive
Plug Type	N
Power Consumption (In Watts)	72

Environmental

Operating Temperature	5C to 45C (41F to 113F)
Storage Temperature	-20C to 50C (-4F to 122F)
Humidity	20% ~ 80% RH

Physical Characteristics

Color	Black
Material	Metal
Product Length	7.7 in [19.5 cm]
Product Width	5.1 in [13.0 cm]
Product Height	0.8 in [2.0 cm]
Weight of Product	1.4 lb [0.6 kg]

Packaging Information

Package Quantity	1
Package Length	9.2 in [23.4 cm]
Package Width	6.2 in [15.7 cm]
Package Height	5.2 in [13.2 cm]
Shipping (Package) Weight	4.1 lb [1.9 kg]

What's in the Box

Included in Package	1 - 4 Bay NVMe TB3 SSD Enclosure
	1 - 2.3 ft (70 cm) Certified Thunderbolt 3 Passive Cable
	1 - Manual
	1 - Universal Power Adapter (NA/JP, UK, EU, ANZ)

****Product appearance and specifications are subject to change without notice.***