2m External Serial Attached SCSI SAS Cable - SFF-8470 to SFF-8088

Product ID: ISAS88702

The ISAS88702 2-meter Serial Attached SCSI Cable is designed for high-performance networks, servers, workstations and desktops. This SAS cable features a SFF-8470 (Infiniband) connector and a SFF-8088 (external mini-SAS) connector that supports data transfer rates up to 6 Gbps.

The SFF-8470 to SFF-8088 SAS cable is constructed of high quality materials and is backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility

Applications

• Connect SAS Controllers to SAS Backplanes

• For use in Storage Area Networks, to connect SAS Expander enabled controllers and enclosures

Features

• Durable metal connectors

• Infiniband plug with thumbscrews for secure connections

• Supports data transfer rates up to 6 Gbps

• Compatible with many servers, including:
IBMMegaRAID 8480
IBM System Storage EXP3000 IBM x3850 (8864)
IBM x3800 (8866)
IBM x3655 (7985)
IBM x3455 (7984,7986)
IBM x3250 (4364,4365)

Hardware		
	Warranty	Lifetime
	Number of Conductors	8 Twisted Pair
	Cable Jacket Material	PVC - Polyvinyl Chloride
	Cable Shield Material	Aluminum-polyester foil with tinned copper braid
Connector(s)		
	Connector A	1 - SFF-8470 (32 pin, Infiniband, External SAS)
	Connector B	1 - SFF-8088 (26-pin, External Mini-SAS)
Physical Characteristics		
	Color	Black
	Wire Gauge	28 AWG
	Cable Length	6.6 ft [2 m]
	Diameter	7.874mm
	Product Length	6.6 ft [2.0 m]
	Product Width	0.0 in [0.0 cm]
	Product Height	0.0 in [0.0 cm]
	Weight of Product	9.5 oz [268.0 g]
Packaging Information		
	Package Quantity	1
	Package Length	13.0 in [33.0 cm]
	Package Width	10.0 in [25.5 cm]
	Package Height	0.9 in [24.0 mm]
	Shipping (Package) Weight	9.5 oz [270.0 g]

What's in the Box

Included in Package	1 - 2m External Serial Attached SCSI SAS Cable - SFF-8470 to SFF-8088

Product appearance and specifications are subject to change without notice.