

## 2m External Serial Attached SCSI SAS Cable - SFF-8470 to SFF-8088

**Product ID:** ISAS88702



The ISAS88702 2-meter Serial Attached SCSI Cable is designed for high-performance networks, servers, workstations and desktops. This SAS cable features a SFF-8470 (Infiniband) connector and a SFF-8088 (external mini-SAS) connector that supports data transfer rates up to 6 Gbps.

The SFF-8470 to SFF-8088 SAS cable is constructed of high quality materials and is backed by StarTech.com's Lifetime Warranty.

### Certifications, Reports and Compatibility

#### Applications

- Connect SAS Controllers to SAS Backplanes
- For use in Storage Area Networks, to connect SAS Expander enabled controllers and enclosures

#### Features

- Compatible with many servers, including:
  - IBM MegaRAID 8480
  - IBM System Storage EXP3000
  - IBM x3850 (8864)
  - IBM x3800 (8866)
  - IBM x3655 (7985)
  - IBM x3455 (7984,7986)
  - IBM x3250 (4364,4365)
- Durable metal connectors
- Supports data transfer rates up to 6 Gbps
- Infiniband plug with thumbscrews for secure connections

---

**Hardware**

Warranty	Lifetime
Number of Conductors	8 Twisted Pair
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-polyester foil with tinned copper braid

---

**Connector(s)**

Connector A	SFF-8470 (32 pin, Infiniband, External SAS)
Connector B	SFF-8088 (26-pin, External Mini-SAS)

---

**Physical Characteristics**

Color	Black
Wire Gauge	28 AWG
Cable Length	6.6 ft [2 m]
Diameter	7.874mm
Product Length	6.6 ft [2.0 m]
Product Width	0.0 in [0.0 mm]
Product Height	0.0 in [0.0 mm]
Weight of Product	9.5 oz [268.0 g]

---

**Packaging Information**

Package Quantity	1
Package Length	13.0 in [33.0 cm]
Package Width	10.0 in [25.5 cm]
Package Height	0.9 in [24.0 mm]
Shipping (Package) Weight	9.5 oz [270.0 g]

---

**What's in the Box**

Included in Package	2m External Serial Attached SCSI SAS Cable - SFF-8470 to SFF-8088
---------------------	---



---

***\*Product appearance and specifications are subject to change without notice.***

