

10/100 Multi Mode Fiber Copper Fast Ethernet Media Converter ST 2 km

Product ID: MCM110ST2EU



The MCM110ST2EU 10/100 Multi Mode ST Fiber Ethernet Media Converter (2 km) creates a cost-effective Ethernet to fiber link, transparently converting to/from 10Base-T or 100Base-Tx Ethernet signals and 100Base-Fx optical signals to extend an Ethernet network connection over a multimode fiber backbone.

The ST media converter supports a maximum multimode fiber optic cable distance of 2km (1.2 miles), providing a simple solution for connecting 10Base-T/100Base-Tx Ethernet networks to remote locations using ST-terminated multimode fiber, while delivering solid network performance and scalability.

Easy to setup and install, this compact, value-conscious fast Ethernet media converter features auto-switching MDI and MDI-X support on the RJ45 UTP connections as well as manual controls for UTP mode, speed, Full and Half Duplex, as well as LFP (Link Fault pass-through) on/off.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Provides connectivity to a user or network segment that is in an isolated area of a large complex or in another building altogether
- Perfect for secure environments required by government agencies where EMI is not acceptable
- Connect traffic control/monitoring systems at extreme distances to the main office
- Extend network connectivity to remote areas of stadiums, auditoriums or other venues
- Converts 10/100Base-T Ethernet to 100Base-FX fiber optic signals over multimode fiber cable

Features

- Supports full or half-duplex operation
- Compatible with 3COM, Cisco, Lucent and Nortel networks
- LED Indicators for simple Ethernet/Fiber network link monitoring
- Support flow control (Pause)
- Supports a maximum multi mode fiber optic cable distance of 2 km
- Supports IEEE 802.1q Tag VLAN pass thru
- Supports IEEE 802.3 10Base-T, 802.3u 100Base-TX and 100Base-FX industry standards
- Supports Link Fault Pass through (LFP)
- Supports Q in Q double tagged frame transparent

Hardware

Warranty	2 Years
PoE	No
WDM	No
Industry Standards	IEEE 802.3 10BASE-T IEEE 802.3u 100BASE-FX IEEE 802.3u 100BASE-TX

Performance

Maximum Data Transfer Rate	10/100Mbps
Max Transfer Distance	2 km (1.2 mi)
Type	Multi Mode
Wavelength	1310nm
Fiber Operating Mode	Half/Full-Duplex
Optical Power	-14 ~ -20 dBm
Sensitivity	-31 dBm

MTBF 65,000 Hours

Power Budget 11 dB

Connector(s)

Local Unit Connectors RJ-45
Fiber Optic ST Duplex

Indicators

LED Indicators Ethernet Link & Activity (ON - Fiber Link ok, Blinking - Activity on Fiber Link)
FEF [Far End Fault](On - Fault Detected, Off - No Fault)
Fiber Link & Activity (On - Fiber Link ok, Blinking - Activity on Fiber Link)
Full (Full duplex / Half duplex)
Power
Speed (10 or 100 Mbps)

Power

Power Source AC Adapter Included
Input Voltage 100 - 240 AC
Output Voltage 12V DC
Output Current 0.2A
Center Tip Polarity Positive
Plug Type M
Power Consumption (In Watts) 2.4

Environmental

Operating Temperature 0C to 50C (32°F to 122F)
Storage Temperature -10C to 70C (14°F to 158F)
Humidity 10~90% RH



Physical Characteristics

Color	Black
Material	Plastic
Product Length	3.0 in [75 mm]
Product Width	3.7 in [95 mm]
Product Height	0.8 in [20 mm]
Weight of Product	3.2 oz [90.5 g]

Packaging Information

Package Length	5.7 in [14.5 cm]
Package Width	6.9 in [17.5 cm]
Package Height	2.6 in [65 mm]
Shipping (Package) Weight	9.9 oz [280 g]

What's in the Box

Included in Package	Media Converter
	Power Adapter
	Instruction Manual

****Product appearance and specifications are subject to change without notice.***

