

2-Port Multi Monitor Adapter - DisplayPort 1.2 MST Hub to Dual 4K 30Hz or 1080p - USB Bus Powered - Multiple Monitors - Video Splitter for Extended Desktop Mode on Windows

**Product ID:** MSTDP122DP



This MST hub lets you connect two monitors to your DisplayPort (DP) 1.2 equipped Windows laptop or desktop. It's USB powered, so the only thing you'll need to operate the hub is your computer.

The newest generations of computers are more portable than ever, which often means that you're left with fewer video outputs and smaller integrated screens. This MST hub solves both of these problems by letting you connect two additional displays to your computer, which makes multitasking much easier.

With the MST hub, you can use DisplayPort video adapters and cable adapters that enable you to connect HDMI, VGA or DVI displays. This ensures your MST hub will be compatible with virtually any television, monitor or projector. The hub is VESA and DisplayPort certified to support DP 1.2 enabled systems, for seamless integration with your existing video equipment.

Using the MST hub, you can extend your desktop onto additional monitors and stream independent content to each display, giving you the freedom to multitask and increase your productivity. You can also mirror the same image onto multiple displays for remote viewing applications such as digital signage.

MST technology uses your existing video card to minimize the use of system resources while delivering Ultra HD 4K resolutions. This unprecedented performance makes MST perfect for high-resolution applications such as graphic design, gaming and medical imaging.

Note: When using a DisplayPort 1.1 video card the MST hub will act as a splitter, automatically mirroring your video source across all displays. Resolution limitations apply.

The MSTDP122DP supports plug-and-play installation for a hassle-free setup, and is backed by a StarTech.com 3-year warranty and free lifetime technical support.

Average resolution bandwidth allocation

1920x1080 (High-definition 1080p) @60hz - 22%  
1920x1200 @60hz - 30%  
2560x1440 @60hz - 35%  
2560x1600 @60hz - 38%  
3840 x 2160 (Ultra HD 4K) @30hz - 38%

<small>Note: Exceeding 100% will reduce functionality.</small>

## Certifications, Reports and Compatibility

### Applications

- Use one screen for reference data such as websites, while composing in another screen
- Dock your DP 1.2 device and add two high-resolution displays to your workstation
- Create a panoramic video wall for DisplayPort digital signage applications
- Edit images, video or audio clips across two additional displays in any orientation or resolution
- Perfect for spanning a spreadsheet or worksheet across two additional displays, to avoid side-scrolling

### Features

- **MULTIPLE MONITORS:** DisplayPort multi monitor adapter drives 2x DP displays (DP 1.2/HBR2/MST/21.6Gbps) at 4K 30Hz or 2x 1080p 60Hz using a DP port on Windows PCs. Extended dual displays not supported on macOS (supports single display or mirrored screen)
- **COMPATIBLE WITH:** 2-Port MST video splitter supports laptops, computers or desktop graphics cards with DP 1.2 video out (supporting MST and HBR2), incl. brands like HP, Dell & Lenovo and AMD & nvidia video cards
- **INCREASE PRODUCTIVITY:** With minimal footprint, this multi-stream transport hub helps increase your productivity by adding extended screens to your workstation at the office/home office
- **EASY TO USE:** Dual monitor adapter uses MST technology to natively support DP monitors delivering uncompressed video; Works w/Windows and provides an easy driverless setup
- **CONVENIENCE:** Equipped w/ built-in 30cm cable for both power (USB Bus powered) and video (DisplayPort), this MST hub won't clutter your workspace and can be used anywhere

---

#### Prominence

Warranty	3 Years
Description CDW 75 - 1st Line	StarTech.com 2-Port Multi Monitor Adapter - DisplayPort MST Hub - Dual 4K

---

#### Hardware

Active or Passive Adapter	Active
Ports	2

AV Input	DisplayPort - 1.2
AV Output	DisplayPort - 1.2
Audio	Yes
Chipset ID	MegaChips - STDP4320

---

### Performance

Maximum Cable Distance To Display	6.6 ft [2 m]
Maximum Digital Resolutions	3840 x 2160 @30hz
Supported Resolutions	1024x768 1280x720 (High-definition 720p) 1920x1080 (High-definition 1080p) 1920x1200 2560x1440 2560x1600 3840 x 2160 (Ultra HD 4K) @30hz
Wide Screen Supported	Yes
Audio Specifications	DisplayPort - 5.1 Channel Audio

---

### Connector(s)

Connector A	DisplayPort (20 pin)
Connector B	DisplayPort (20 pin)

---

### Software

OS Compatibility	Windows 10 (32/64) Windows 8/8.1 (32/64) Windows 7(32/64)
------------------	---

---

### Special Notes / Requirements

Note	DisplayPort 1.2 with MST+HBR2 support from the GPU is required for independent display output
------	---

---

### Power



Power Source	USB-Powered
--------------	-------------

---

**Environmental**

Operating Temperature	0C to 40C (32F to 104F)
Storage Temperature	-20C to 60C (-4F to 140F)
Humidity	50-90%

---

**Physical Characteristics**

Color	Black
Material	Plastic
Cable Length	7.5 in [19 cm]
Product Length	15.2 in [38.6 cm]
Product Width	2.3 in [58 mm]
Product Height	0.6 in [14 mm]
Weight of Product	1.8 oz [52 g]

---

**Packaging Information**

Package Length	6.8 in [17.2 cm]
Package Width	5.6 in [14.1 cm]
Package Height	1.2 in [30 mm]
Shipping (Package) Weight	4.7 oz [134 g]

---

**What's in the Box**

Included in Package	2-port DP MST Hub
	Quick install guide

---

***\*Product appearance and specifications are subject to change without notice.***

