

## 35 ft Coax High Resolution VGA Monitor Extension Cable - HD15 M/F

**Product ID:** MXT101HQ35



This 35ft High Resolution VGA Extension Cable is designed to provide the highest video quality possible through VGA.

Ideally suited for high resolution VGA applications, this high quality male to female coaxial VGA extension cable helps to eliminates picture "ghosting" and fuzzy images inherent to non-coaxial cables, and provides superior EMI interference protection by using ferrite cores near the connector ends.

### Certifications, Reports and Compatibility



### Applications

#### Features

- Triple-coaxial + twisted-pair wire for crystal clear display
- Impedance matched at 75 Ohms for full brightness and vibrant picture color
- Ferrite core eliminates EMI interference
- Molded connector ends with strain relief
- Ideal for high resolution monitors (1920x1200 and above)

---

#### Hardware

Warranty	Lifetime
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride

---

#### Connector(s)

Connector A	1 - VGA (15 pin, High Density D-Sub)
Connector B	1 - VGA (15 pin, High Density D-Sub)

---

#### Special Notes / Requirements

Note	Pin number 9 is not populated on these connectors
------	---

---

#### Physical Characteristics

Color	Gray
Wire Gauge	28 AWG
Cable Length	35.0 ft [10.7 m]
Product Length	35.0 ft [10.7 m]
Product Width	0.0 in [0.0 cm]
Product Height	0.0 in [0.0 cm]
Weight of Product	2.3 lb [1.1 kg]

---

#### Packaging Information

Package Quantity	1
Package Length	8.4 in [21.3 cm]
Package Width	8.7 in [22.1 cm]
Package Height	2.7 in [6.9 cm]
Shipping (Package) Weight	2.4 lb [1.1 kg]

---

#### What's in the Box

Included in Package	35 ft Coax High Resolution VGA Monitor Extension Cable -
---------------------	--

HD15 M/F

---

**Warranty  
Information**

Warranty

Lifetime

---

***\*Product appearance and specifications are subject to change without notice.***