

## Mini DisplayPort to DVI Active Adapter

Product ID: MDP2DVIS



The MDP2DVIS Mini DisplayPort to DVI Active Adapter (single-link) lets you connect your Mini DisplayPort video source (such as any of your MacBook or Microsoft Surface Pro devices with mDP) to a DVI-D display, including televisions and Apple Cinema Display HD, eliminating the expense of having to upgrade to a DisplayPort capable monitor.

Unlike passive video adapters, this Mini DisplayPort to DVI adapter offers an active conversion for use with any Mini DisplayPort output - ideal for graphics cards that are not capable of outputting multi-mode DP++ signals (e.g. ATI Eyefinity).

Supporting resolutions up to 1920x1200, this compact device provides a simple solution for adapting PC or Mac Mini-DisplayPort output for DVI monitors, televisions or projectors.

The Mini DP to DVI adapter is compatible with Intel Thunderbolt, when connected directly to a supporting DisplayPort over Thunderbolt I/O port.

Backed by a StarTech.com 3-year warranty and free lifetime technical support.

## Certifications, Reports and Compatibility



## Applications

- Ideal for digital entertainment centers, home offices, business conference rooms and trade show displays
- Ideal for using your DVI monitor as a secondary display
- Keep your existing DVI monitor to be used with your new Mini DisplayPort device
- Perfect for larger format screens that use high DVI resolutions

- Adapt from graphics cards that are not capable of outputting DP++ signals

## Features

- Compliant with DisplayPort 1.1a specifications
- Supports HDCP 1.3
- Supports display resolutions up to 1920x1200 at 60Hz
- Works with video cards that aren't capable of outputting DP++ (multi-mode) signals
- Compatible with Intel Thunderbolt

<b>Hardware</b>	Warranty	3 Years
	Active or Passive Adapter	Active
	AV Input	Mini DisplayPort - 1.2
	AV Output	DVI-D - Single-Link
	Audio	No
	Fire Rating	LSZH Rated (Low Smoke Zero Halogen)
	Industry Standards	HDCP 1.3
		DisplayPort 1.1
DDWG 1.0		
<b>Performance</b>	Maximum Digital Resolutions	1920x1200
	Supported Resolutions	1920x1200 / 60Hz
	Wide Screen Supported	Yes
	Audio Specifications	DVI - No Audio Support
<b>Connector(s)</b>	Connector A	Mini-DisplayPort (20 pin)
	Connector B	DVI-D (25 pin)
<b>Environmental</b>	Operating Temperature	0C to 70C (32F to 158F)
	Storage Temperature	0C to 70C (32F to 158F)
<b>Physical Characteristics</b>	Color	Black
	Cable Length	4.7 in [1.2 cm]
	Product Length	7.9 in [2.0 cm]
	Product Width	1.7 in [44.000 mm]
	Product Height	0.8 in [20.000 mm]
	Weight of Product	1.3 oz [38.000 g]

---

<b>Packaging Information</b>	Package Length	8.7 in [2.2 cm]
	Package Width	7.9 in [2.0 cm]
	Package Height	0.7 in [19.000 mm]
	Shipping (Package) Weight	1.7 oz [47.000 g]

---

<b>What's in the Box</b>	Included in Package	Mini-DisplayPort to DVI Adapter
--------------------------	---------------------	---------------------------------

---

*\*Product appearance and specifications are subject to change without notice.*

