

75 ft Coax High Resolution VGA Monitor Extension Cable - HD15 M/F

Product ID: MXT101HQ75



This 75ft High Resolution VGA Extension Cable is designed to provide the highest video quality possible through VGA.

Ideally suited for high resolution VGA applications, this high quality male to female coaxial VGA extension cable helps to eliminate picture "ghosting" and fuzzy images inherent to non-coaxial cables, and provides superior EMI interference protection by using ferrite cores near the connector ends.

Certifications, Reports and Compatibility

Applications

Features

- Triple-coaxial + twisted-pair wire for crystal clear display
- Impedance matched at 75 Ohms for full brightness and vibrant picture color
- Ferrite core eliminates EMI interference
- Molded connector ends with strain relief
- Ideal for high resolution monitors (1920x1200 and above)

Hardware

Warranty

Lifetime

Cable Jacket Material	PVC - Polyvinyl Chloride
-----------------------	--------------------------

Connector(s)

Connector A	VGA (15 pin, High Density D-Sub)
Connector B	VGA (15 pin, High Density D-Sub)

Physical Characteristics

Color	Black
Wire Gauge	28 AWG
Cable Length	75.0 ft [22.9 m]

Packaging Information

Package Length	11.4 in [29 cm]
Package Width	2.4 in [60 mm]
Package Height	17.3 in [44 cm]
Shipping (Package) Weight	4.8 lb [2.2 kg]

What's in the Box

Included in Package	75 ft Coax High Resolution VGA Monitor Extension Cable - HD15 M/F
---------------------	---

**Product appearance and specifications are subject to change without notice.*

