

## 100 ft Coax High Resolution VGA Monitor Extension Cable - HD15 M/F

**Product ID:** MXT101HQ\_100



This 100ft High Resolution VGA Extension Cable is designed to provide the highest video quality possible through VGA.

Ideally suited for high resolution VGA applications, this high quality male to female coaxial VGA extension cable helps to eliminate picture "ghosting" and fuzzy images inherent to non-coaxial cables, and provides superior EMI interference protection by using ferrite cores near the connector ends.

### Certifications, Reports and Compatibility



### Applications

- Extends your VGA monitor cable

### Features

- Triple-coaxial + twisted-pair wire for crystal clear display
- Impedance matched at 75 Ohms for full brightness and vibrant picture color
- Molded connector ends with strain relief
- Ideal for high resolution monitors (1920x1200 and above)

- Ferrite core eliminates EMI interference

---

#### Connector(s)

Warranty	Lifetime
Connector A	1 - VGA (15 pin, High Density D-Sub)
Connector B	1 - VGA (15 pin, High Density D-Sub)

---

#### Special Notes / Requirements

Note	Pin number 9 is not populated on these connectors
------	---

---

#### Physical Characteristics

Color	Black
Wire Gauge	28 AWG
Cable Length	100.0 ft [30.5 m]
Product Length	100.0 ft [30.5 m]
Product Width	0.0 in [0.0 cm]
Product Height	0.0 in [0.0 cm]
Weight of Product	6.2 lb [2.8 kg]

---

#### Packaging Information

Package Quantity	1
Package Length	14.0 in [35.5 cm]
Package Width	2.2 in [5.6 cm]
Package Height	18.0 in [45.8 cm]
Shipping (Package) Weight	6.2 lb [2.8 kg]

---

#### What's in the Box

Included in Package	1 - 100 FOOT COAXIAL CABLE
	2 - Nuts

---

**Warranty  
Information**

Warranty

Lifetime

---

***\*Product appearance and specifications are subject to change without notice.***