

50 ft Coax High Resolution VGA Monitor Extension Cable - HD15 M/F

Produkt ID: MXT101HQ_50



The MXT101HQ_50 High Resolution VGA Extension Cable (50ft) is designed to extend your VGA video connection while maintaining the highest video quality possible through VGA.

Ideally suited for high resolution VGA video applications, this high quality coaxial VGA extension cable (HD15 to HD15, M-F) helps eliminate the picture ghosting and fuzzy images that are inherent to non-coaxial cables, and features ferrite cores near the VGA connector ends to protect against EMI interference.

Certifikat, rapporter och kompatibilitet



Användning

- Extend your SVGA/VGA cable, for more convenient monitor placement
- Extend the connection distance between monitors, video splitters, projectors and a VGA video source

Funktioner

- Triple coaxial + twisted-pair wire for crystal clear display
- Durably constructed cable, with high quality HD15 connectors

- Impedance matched at 75 Ohms for full brightness and vibrant picture color from your VGA monitor
- High quality VGA connectors with molded PVC strain relief
- Ferrite cores to help eliminate EMI interference

Hårdvara

Garantipolicy	Lifetime
Kontaktplätering	Nickel

Kontakt(er)

Connector A	1 - VGA (15-stifts, High Density D-Sub)
Connector B	1 - VGA (15-stifts, High Density D-Sub)

Särskilda anmärkningar/krav

Obs.	Pin number 9 is not populated on these connectors
------	---

Utseende

Färg	Svart
Tråddimension	28 AWG
Kabellängd	50.0 ft [15.2 m]
Produktlängd	50.0 ft [15.2 m]
Produktbredd	0.0 in [0.0 mm]
Produkthöjd	0.0 in [0.0 mm]
Produktvikt	3.3 lb [1.5 kg]

Förpackning

Förpackningsantal	1
Paketets längd	11.9 in [30.3 cm]
Paketets bredd	9.6 in [24.5 cm]
Paketets höjd	3.0 in [7.7 cm]

Fraktvikt (förpackning) 3.4 lb [1.5 kg]

Vad det är i lådan

Ingår i paketet	1 - 50 ft Coax High Resolution VGA Monitor Extension Cable - HD15 M/F
	2 - Nuts

Warranty
Information

Warranty	Livslängd
----------	-----------

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.