

15ft Coax High Resolution 90° Down Angled VGA Monitor Cable - HD15 M/M

Product ID: MXT101MMHD15



This 15ft High Resolution Video VGA Cable (90 degree) is designed to provide the highest video quality possible through a VGA connection and is specifically constructed to accommodate tight installation spaces.

The high quality, shielded coax VGA cable features a 90 degree down-angled plug, which requires only 32.4mm (1.27") of space to make the video connection.

More than suitable for high-res VGA applications (1280x1024 resolution and above), the 90 degree VGA cable eliminates picture "ghosting" and fuzzy images that are common with non-coaxial cables, and provides superior EMI interference protection using ferrite cores near the connector ends.

Certifications, Reports and Compatibility



Applications

- Connecting Multimedia Servers
- POS Displays
- Ideal for high resolution monitors (1280x1024 and above)
- Making VGA video connections in tight install spaces

Features

- Ferrite core to preserve signal integrity
- Ideal for high resolution monitors (1280x1024 and above)
- Impedance matched at 75 Ohms
- Triple-coaxial + twisted-pair wire construction
- Molded connector ends with strain relief
- 90 downward-angled connector with a 32.4mm depth

Hardware

Warranty	Lifetime
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Number of Ferrites	1

Connector(s)

Connector A	1 - VGA (15 pin, High Density D-Sub)
Connector B	1 - VGA (15 pin, High Density D-Sub)

Physical Characteristics

Color	Black
Wire Gauge	28 AWG
Cable Length	15.0 ft [4.6 m]
Product Length	15.0 ft [4.6 m]
Weight of Product	17.2 oz [487 g]

Packaging Information

Package Quantity	1
Package Length	6.7 in [16.9 cm]
Package Width	7.7 in [19.5 cm]
Package Height	2.2 in [5.5 cm]

Shipping (Package) Weight	1.0 lb [0.5 kg]
------------------------------	-----------------

What's in the Box

Included in Package	1 - 15ft Coax High Resolution 90 Down Angled VGA Monitor Cable - HD15 M/M
---------------------	--

**Warranty
Information**

Warranty	Lifetime
----------	----------

****Product appearance and specifications are subject to change without notice.***