

6 ft Coax High Resolution 90° Down Angled VGA Monitor Cable - HD15 M/M

Product ID: MXT101MMHD6



This 6ft High Resolution Video VGA Cable (90 degree) is designed to provide the highest video quality possible through a VGA connection and is specifically constructed to accommodate tight installation spaces.

The high quality, shielded coax VGA cable features a 90 degree down-angled plug, which requires only 32.4mm (1.27") of space to make the video connection.

More than suitable for high-res VGA applications (1280x1024 resolution and above), the 90 degree VGA cable eliminates picture "ghosting" and fuzzy images that are common with non-coaxial cables, and provides superior EMI interference protection using ferrite cores near the connector ends.

Certifications, Reports and Compatibility



Applications

- Connecting Multimedia Servers
- POS Displays
- Ideal for high resolution monitors (1280x1024 and above)
- Making VGA video connections in tight install spaces

Features

- Ferrite core
- Triple-coaxial + twisted-pair wire construction
- Molded connector ends with strain relief
- Impedance matched at 75 Ohms
- 90 downward-angled connector with a 32.4mm depth
- Ideal for high resolution monitors (1280x1024 and above)

Hardware

Warranty	Lifetime
Cable Jacket Material	PVC - Polyvinyl Chloride
Number of Ferrites	1

Connector(s)

Connector A	1 - VGA (15 pin, High Density D-Sub)
Connector B	1 - VGA (15 pin, High Density D-Sub)

Physical Characteristics

Color	Black
Wire Gauge	28 AWG
Cable Length	6.0 ft [1.8 m]
Product Length	6.0 ft [1.8 m]
Product Width	0.0 in [0.0 cm]
Product Height	0.0 in [0.0 cm]
Weight of Product	8.3 oz [236.0 g]

Packaging Information

Package Quantity	1
Package Length	8.7 in [22.0 cm]
Package Width	7.9 in [20.0 cm]

Package Height	1.0 in [2.5 cm]
Shipping (Package) Weight	8.6 oz [245.0 g]

What's in the Box

Included in Package	1 - 6ft Coax High Resolution Down Angle VGA Monitor Cable
---------------------	---

Warranty Information

Warranty	Lifetime
----------	----------

****Product appearance and specifications are subject to change without notice.***