

65 ft Coax High Resolution Monitor VGA Cable - HD15 M/M

**Product ID:** MXT101MMHQ65



This 65-foot High Resolution VGA Monitor Cable is designed to provide the highest video quality possible through VGA. Ideally suited for high resolution VGA applications, this high quality male-to-male coaxial VGA cable eliminates the picture "ghosting" and fuzzy images that are inherent to non-coaxial cables, while providing superior EMI interference protection by using ferrite cores near the connector ends.

## **Certifications, Reports and Compatibility**

### **Applications**

- Connect any VGA display to a VGA source
- Easily connect a High resolution display to a Desktop PC using VGA

### **Features**

- Supports high resolution applications(1920x1200 and above)
  - Ferrite core eliminates EMI interference
  - Impedance matched at 75 Ohms for full brightness and vibrant picture color
  - Molded connector ends with strain relief
  - Triple-coaxial and twisted-pair wire for crystal clear display
-

## Hardware

Warranty	Lifetime
Number of Conductors	14
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid
Fire Rating	CMG Rated (General Purpose)
Number of Ferrites	1

---

## Connector(s)

Connector A	VGA (15 pin, High Density D-Sub)
Connector B	VGA (15 pin, High Density D-Sub)

---

## Environmental

Operating Temperature	0 to 60 C
Storage Temperature	-20 to 80 C
Humidity	0 - 80 %RH

---

## Physical Characteristics

Color	Black
Connector Style	Straight
Wire Gauge	28 AWG
Cable Length	65.0 ft [19.8 m]
Weight of Product	4.1 lb [1.8 kg]

---

## Packaging Information

Package Quantity	1
Package Length	13.9 in [35.2 cm]
Package Width	18.1 in [46 cm]
Package Height	0.4 in [10 mm]



Shipping (Package) Weight	4.1 lb [1.9 kg]
------------------------------	-----------------

---

**What's in the  
Box**

Included in Package	65 ft Coax monitor Cable
---------------------	--------------------------

---

***\*Product appearance and specifications are subject to change without notice.***

