

60 ft Coax High Resolution Monitor VGA Cable - HD15 M/M

Product ID: MXT101MMHQ60



The MXT101MMHQ60 High Resolution VGA Cable (60ft) is designed to provide the highest video quality possible through VGA, ideally suited for high resolution applications of 1920x1200 and above.

This durably constructed coaxial VGA video cable (HD15 to HD15) eliminates the picture "ghosting" and fuzzy images that are inherent to non-coaxial VGA cables, while delivering superior EMI interference protection by using ferrite cores near the connector ends.

Certifications, Reports and Compatibility



Applications

- Replace a worn-out or missing VGA monitor cable with this high quality, coax VGA cable
- Supports high resolution VGA monitors (1920x1200)
- Connect a high resolution display to a Desktop PC or video switch, up to 60 feet away

Features

- Triple-coaxial + twisted-pair wire for crystal clear display
- Durably constructed cable, with high quality HD15 connectors
- Impedance matched at 75 Ohms for full brightness and vibrant picture color from your VGA monitor
- High quality VGA connectors with molded PVC strain relief

Hrdvara	Warranty	Lifetime
	Antal ledare	14

Kontaktpåtering	Nickel
Kabelmanteltyp	PVC - Polyvinyl Chloride
Kabelskärmning	Aluminum-Mylar Foil with Braid
Brandteknisk klass	CMG Rated (General Purpose)
Antal ferriter	1

Kontakt(er)	Connector A	VGA (15 pin, High Density D-Sub)
	Connector B	VGA (15 pin, High Density D-Sub)

Miljö	Drifttemperatur	0 to 60 C
	Förvaringstemperatur	-20 to 80 C
	Luftfuktighet	0 - 80 %RH

Utseende	Färg	Black
	Tråddimension	28 AWG
	Kabel längd	60.0 ft [18.3 m]
	Produktlängd	60.0 ft [18.3 m]
	Produktvikt	3.7 lb [1.7 kg]

Förpackning	Förpackningsantal	1
	Package Length	18.1 in [4.6 cm]
	Package Width	13.8 in [3.5 cm]
	Package Height	3.6 in [92 mm]
	Fraktvikt (förpackning)	3.8 lb [1.7 kg]

Vad det r i ldan	Inger i paketet	60 ft Coax High Resolution Monitor VGA Cable - HD15 M/M
-------------------------	-----------------	---

****Product appearance and specifications are subject to change without notice.***

