

10 ft Coax High Resolution 90° Upward Angled VGA Monitor Cable - HD15 M/M

Product ID: MXT101MMHU10



This 10ft upward-angle VGA cable is designed to support the highest resolutions and highest video quality possible through VGA while fitting perfectly in tight connection spaces. The cable features one standard VGA connector (HD15) and one VGA connector (HD15) that is situated on an upward angle relative to the shaft of the cable, requiring only 32.4mm of space at the connection point.

Suited for high resolution VGA applications (1280x1024 and above), this high quality coaxial VGA cable eliminates picture "ghosting" and fuzzy images inherent to non-coaxial cables, and provides superior EMI interference protection using ferrite cores near the connector ends.

Certifications, Reports and Compatibility



Applications

- Connecting Multimedia Servers
- POS Displays

Features

- 90 Upward Angled connector with a 32.4mm depth
- Ferrite core eliminates EMI interference

- Ideal for high resolution monitors (1280x1024 and above)
- Impedance matched at 75 Ohms for full brightness and vibrant picture color
- Molded connector ends with strain relief
- Triple-coaxial + twisted-pair wire for crystal clear display

Hardware

Warranty	Lifetime
Cable Jacket Material	PVC - Polyvinyl Chloride
Number of Ferrites	1

Connector(s)

Connector A	1 - VGA (15 pin, High Density D-Sub)
Connector B	1 - VGA (15 pin, High Density D-Sub)

Physical Characteristics

Color	Black
Wire Gauge	28 AWG
Cable Length	10.0 ft [3.0 m]
Weight of Product	11.8 oz [334 g]

Packaging Information

Package Quantity	1
Package Length	6.7 in [17.1 cm]
Package Width	1.5 in [37 mm]
Package Height	8.1 in [20.6 cm]
Shipping (Package) Weight	0.7 lb [0.3 kg]

What's in the Box

Included in Package	1 - 10ft Coax High Resolution Up Angle VGA Monitor Cable
---------------------	----------------------------------------------------------

Warranty Information

Warranty

Lifetime

****Product appearance and specifications are subject to change without notice.***