

65 ft Coax High Resolution Monitor VGA Cable - HD15 M/M

Produkt ID: MXT101MMHQ65



This 65-foot High Resolution VGA Monitor Cable is designed to provide the highest video quality possible through VGA. Ideally suited for high resolution VGA applications, this high quality male-to-male coaxial VGA cable eliminates the picture "ghosting" and fuzzy images that are inherent to non-coaxial cables, while providing superior EMI interference protection by using ferrite cores near the connector ends.

Certifikat, rapporter och kompatibilitet



Användning

- Connect any VGA display to a VGA source
- Easily connect a High resolution display to a Desktop PC using VGA

Funktioner

- Supports high resolution applications(1920x1200 and above)
- Ferrite core eliminates EMI interference
- Impedance matched at 75 Ohms for full brightness and vibrant picture color

- Molded connector ends with strain relief
- Triple-coaxial and twisted-pair wire for crystal clear display

Hårdvara

Garantipolicy	Lifetime
Antal ledare	14
Kontaktplätering	Nickel
Kabelmanteltyp	PVC - Polyvinyl Chloride
Kabelskärmning	Aluminiummylarfolie med flätning
Brandteknisk klass	CMG-klass (General Purpose)
Antal ferriter	1

Kontakt(er)

Connector A	1 - VGA (15-stifts, High Density D-Sub)
Connector B	1 - VGA (15-stifts, High Density D-Sub)

Miljö

Drifttemperatur	0 to 60 °C
Förvaringstemperatur	-20 to 80 °C
Luftfuktighet	0 - 80 %RH

Utseende

Färg	Svart
Kontakttyp	Rak
Tråddimension	28 AWG
Kabellängd	65.0 ft [19.8 m]
Produktvikt	4.1 lb [1.8 kg]

Förpackning

Förpackningsantal	1
-------------------	---

Paketets längd 13.9 in [35.2 cm]

Package Width 18.1 in [46 cm]

Paketets höjd 0.4 in [10 mm]

Fraktvikt (förpackning) 4.1 lb [1.9 kg]

Vad det är i lådan

Ingår i paketet 1 - 65 ft Coax monitor Cable

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.