

## 70 ft Coax High Resolution Monitor VGA Cable - HD15 M/M

**Product ID:** MXT101MMHQ70



This 70-foot High Resolution VGA Monitor Cable is designed to provide the highest video quality possible through VGA. Ideally suited for high resolution VGA applications, this high quality male-to-male coaxial VGA cable eliminates the picture "ghosting" and fuzzy images that are inherent to non-coaxial cables, while providing superior EMI interference protection by using ferrite cores near the connector ends.

### Certifications, Reports and Compatibility



### Applications

- Perfect for error-free performance over long distances
- Easily connect a high resolution display to a Desktop PC using VGA

### Features

- Supports high resolution applications(1920x1200 and above)
- Ferrite core eliminates EMI interference
- Impedance matched at 75 Ohms for full brightness and vibrant picture color
- Molded connector ends with strain relief

- Triple-coaxial + twisted-pair wire for crystal clear display

---

#### Hardware

Warranty	Lifetime
Number of Conductors	14
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid
Fire Rating	CMG Rated (General Purpose)
Number of Ferrites	1

---

#### Connector(s)

Connector A	1 - VGA (15 pin, High Density D-Sub)
Connector B	1 - VGA (15 pin, High Density D-Sub)

---

#### Environmental

Operating Temperature	0 to 60 C
Storage Temperature	-20 to 80 C
Humidity	0 - 80 %RH

---

#### Physical Characteristics

Color	Black
Connector Style	Straight
Wire Gauge	28 AWG
Cable Length	70.0 ft [21.3 m]
Weight of Product	4.4 lb [2.0 kg]

---

#### Packaging Information

Package Quantity	1
Package Length	13.9 in [35.2 cm]

Package Width	18.1 in [46 cm]
Package Height	0.4 in [10 mm]
Shipping (Package) Weight	4.4 lb [2 kg]

---

#### What's in the Box

Included in Package	1 - 70 ft Coax monitor Cable
---------------------	------------------------------

---

#### Warranty Information

Warranty	Lifetime
----------	----------

---

***\*Product appearance and specifications are subject to change without notice.***