

15m Coax High Resolution Monitor VGA Cable - HD15 M/M

Product ID: MXTMMHQ15M



The MXTMMHQ15M High Resolution VGA Cable (15-meter) is designed to provide the highest video quality possible through VGA, ideally suited for high resolution applications of 1920x1200 and above.

This durably constructed coaxial VGA video cable (HD15 to HD15) eliminates the picture "ghosting" and fuzzy images that are inherent to non-coaxial VGA cables, while delivering superior EMI interference protection by using ferrite cores near the connector ends.

Certifications, Reports and Compatibility

Applications

- Supports high resolution VGA monitors (1920x1200)
- Create a longer connection between a high resolution VGA display and a desktop PC/video switch than a typical cable length would allow
- Replace a worn-out or missing VGA monitor cable with this high quality, coax VGA cable

Features

- Impedance matched at 75 Ohms for full brightness and vibrant picture color from your VGA monitor
- High quality VGA connectors with molded PVC strain relief
- Triple coaxial + twisted-pair wire for crystal clear display
- Durably constructed cable, with high quality HD15 connectors

Hardware

Warranty	Lifetime
Number of Conductors	14
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid
Fire Rating	CMG Rated (General Purpose)
Number of Ferrites	1

Connector(s)

Connector A	VGA (15 pin, High Density D-Sub)
Connector B	VGA (15 pin, High Density D-Sub)

Environmental

Operating Temperature	0 to 60 C
Storage Temperature	-20 to 80 C
Humidity	0 - 80 %RH

Physical Characteristics

Color	Black
Wire Gauge	28 AWG
Cable Length	49.2 ft [15 m]
Product Length	49.2 ft [15 m]
Weight of Product	3.1 lb [1.4 kg]

Packaging Information

Package Quantity	1
Package Length	13.0 in [33 cm]
Package Width	10.0 in [25.5 cm]



Package Height 2.4 in [61 mm]

Shipping (Package) Weight 3.1 lb [1.4 kg]

What's in the Box

Included in Package 15m Coax High Resolution Monitor VGA Cable - HD15 M/M

****Product appearance and specifications are subject to change without notice.***

