

Declaration of Conformity

August 13, 2025

To whom it may concern,

I declare that this declaration is issued under the sole responsibility of StarTech.com and that the above product conforms to all the applicable requirements of Directives and Regulations as indicated in this document.

Product Number: N6PATCH10BL10PK

10 ft. CAT6 Ethernet cable - 10 Pack - Blue CAT6 Patch Cord - Snagless RJ45 Connectors - 24 AWG Copper Wire – UTP Ethernet Cable



Nirav Gandhi
Vice President, Product Development

StarTech.com Ltd.

E prodcompliance@startech.com

T (519) 455-9675

T (800) 265-1844

F (519) 455-9425

Regulations	Test Standards
RoHS Directive 2011/65/EU & 2015/863 REACH Regulation EC 1907/2006	This StarTech.com part number is in compliance with the European Directive 2011/65/EU on the Restriction of Hazardous Substances (RoHS) that include Pb, Hg, Cd, Cr6+, PBB, and PBDE. The product is also compliant to the amendment Directive (EU) 2015/863, which added four more substances that include DEHP, BBP, DBP, and DIBP. The RoHS exemptions that apply to this product are: None This product is also compliant with the REACH Regulation (EC) No. 1907/2006 of the European Parliament and of the Council of 18 December 2006, concerning the Registration, Evaluation, Authorization, and Restriction of Chemicals (REACH). The product and its components do not contain any of the Candidate listed 240 Substances of Very High Concern (SVHC) above the threshold of 0.1% by weight. None of the 73 Restricted Substances listed in Annex XVII are present in excess of thresholds set by the regulation.
Persistent Organic Pollutants (POPs) EC No 2019/1021	As per the EU Persistent Organic Pollutants Regulation (EU) 2019/1021 and Stockholm Convention, this StarTech.com product is free of the listed substance or falls under an exemption.
WEEE Directive EC No 850/2004	The European Directive 2012/19/EU on Waste Electrical and Electronic Equipment (WEEE)
Packaging Directive 94/62/EC	The European Packaging and Packaging Waste Directive 94/62/EC