

15ft CAT6 Ethernet Cable - White CAT 6 Gigabit Ethernet Wire -250MHz 100W PoE RJ45 UTP Network/Patch Cord Snagless w/Strain Relief Individually Tested

ID del Producto: N6PATCH15WH



The N6PATCH15WH Cat 6 Patch Cable (15 ft) meets or exceeds all Category 6 cable specifications to ensure reliable Gigabit network connections, and features a durable white PVC jacket that enables you to color code your network cable runs as needed.

To ensure long-lasting performance, this high quality Cat 6 patch cable features a snagless design that protects the RJ45 connector clips from damage and makes the cable less prone to snagging during installation. The cable also features molded PVC strain relief that prevents the RJ45 connector termination points from bending at sharp angles - reducing the risk of cable damage, which could decrease network performance.

Constructed of only top quality materials, this Cat 6 Patch Cord delivers reliable performance and is backed by our Lifetime Warranty.

StarTech.com Cat6 cables are manufactured using high-quality copper conductors. While many cable manufacturers offer a "cheaper" cable based on a copper-coated aluminum core, we make no compromises on quality to ensure you receive top value and performance for your network cable investment.

This Cat6 cable is constructed with 24 gauge copper wire, to support a broad range of Ethernet applications such as Power over Ethernet (PoE). Because we use a high quality copper wire, our cables easily sustain the power required for Power over Ethernet applications, whereas the inferior quality offered by copper-coated aluminum cables may be subject to insufficient power delivery, heat buildup, equipment damage and potentially, fire.

This Cat 6 patch cable offers high quality connectors comprised of 50-micron gold, to deliver optimum conductivity while eliminating signal loss due to oxidation or corrosion.

Certificaciones, Reportes y Compatibilidad



Aplicaciones

- Designed for use with Gigabit networks
- Patches from hub to distribution panel
- Connects workstation to wall outlet
- Extend the reach of your Gigabit network devices by 15 ft

Características

- High quality 24 AWG copper wire
- ANSI/TIA-568-2.D Category 6 Compliance
- HIGH PERFORMANCE CAT6 ETHERNET CABLE: 100% copper for error-free Multi Gigabit 1/2.5/5Gbps connections; 10Gbps up to 160'; Individually Tested to comply w/ANSI/TIA-568-2.D Category 6
- POE SUPPORT: 24 AWG stranded copper conductors & UL Rated Wiring (E132276-A) supports up to 100W for PoE devices like VOIP phone & security systems; IEEE 802.3bt & DTE power compliance reduces cable heating
- QUALITY CONSTRUCTION: UL certified wire; 50-micron gold-plated connectors prevent rust/corrosion to avoid costly network downtime; High quality PVC jacket resists bending or fraying damage
- EASY INSTALLATION: 15 foot snagless patch cord for easy installation & flexible disconnection in wiring conduits; Compatible w/Cat5e & earlier standards; Molded boots available for constrained spaces
- SPECS: Length: 15ft (4.6m) | Color: White | 250 MHz Rated | Structure: 4 Pair UTP | RJ45 | Jacket: PVC | Wire Gauge: 24 AWG Copper | Wiring: ANSI/T568B | Warranty: Lifetime

Hardware

Política de Garantía	Lifetime
Cantidad de Conductores	4 Pair UTP

	Cable Tipo Jacket	PVC - Polyvinyl Chloride
	Grado de Inflamabilidad	Clasificación CMG (uso general)
	Estándar de Cableado	TIA/EIA-568-B.1-2001 T568B
Rendimiento	Clasificación de Cables	CAT6 - 250 MHz
Conector(es)	Conector A	1 - RJ-45
	Conector B	1 - RJ-45
Requisitos Ambientales	Temperatura Operativa	-20°C to 80°C (-4°F to 176°F)
	Temperatura de Almacenamiento	-20°C to 80°C (-4°F to 176°F)
	Humedad	15 ~ 65%
Características Físicas	Color	Blanco
	Calibre del Conductor	24 AWG
	Tipo de conductor	Cobre trenzado
	Longitud del Cable	15.0 ft [4.6 m]
	Longitud del Producto	15.0 ft [4.6 m]
	Peso del Producto	7.4 oz [211 g]
Información de la Caja	Cantidad de Paquetes	1
	Longitud de la Caja	7.4 in [18.8 cm]
	Ancho de la Caja	0.8 in [20 mm]

Altura de la Caja 8.4 in [21.2 cm]

Peso (de la Caja) del Envío 7.4 oz [211 g]

Contenido de la Caja

Incluido en la Caja 1 - 15 ft White Snagless Cat6 UTP Patch Cable - ETL Verified

Información Acerca de la Garantía

Warranty De Por Vida

* La apariencia y las especificaciones del producto están sujetas a cambios sin previo aviso.