

6in CAT6 Ethernet Cable - White CAT 6 Gigabit Ethernet Wire -650MHz 100W PoE RJ45 UTP Network/Patch Cord Snagless w/Strain Relief Fluke Tested/Wiring is UL Certified/TIA

Product ID: N6PATCH6INWH



This Cat6 cable delivers reliable Gigabit network connections, which ensures high-performance capability for your demanding Ethernet applications.

This 6-inch white patch cable is perfect for use in server closets, patch panels and with Ethernet hubs. The cable is intended for short-distance applications such as point-to-point in-rack and across-rack network switch and server connections.

For easier network installations, our Cat6 patch cables are available in a wide variety of lengths and colors. This ensures you have the right size of cable available when you need it and it lets you color code your connections for a more organized setup.

For trouble-free cable runs, this durable cable features snagless connectors that protect the RJ45 clips during installation, making them less likely to snag or break.

The cable also features molded boots which offer connector strain relief by stopping the RJ45 connector termination points from bending at sharp angles. This reduces the risk of damage to the cable, which could decrease network connectivity and performance.

Get the highest value for your cable investment with our Cat6 Ethernet cables. Each of our patch cables is manufactured using high-quality copper conductors and they are carefully constructed and tested, to keep Near-End Crosstalk (NEXT) well within acceptable limits.

Ensure high-performance capability for your demanding Ethernet applications, such as Power-over-Ethernet and 4K or 1080p video streaming, using cables that include 24 AWG copper.

You can rely on our RJ45 connectors to deliver optimum conductivity while eliminating signal loss due to oxidation or corrosion.

The N6PATCH6INWH is backed by StarTech.com's lifetime warranty for guaranteed reliability.

Certifications, Reports and Compatibility



Applications

- Designed for use with Gigabit networks
- Patches from hub to distribution panel
- Connects workstation to wall outlet

Features

- **HIGH PERFORMANCE CAT6 ETHERNET CABLE:** 100% copper for error-free Multi Gigabit 1/2.5/5Gbps connections; 10Gbps up to 160'; Fluke patch cord tested to comply w/ANSI/TIA-568-2.D Category 6
- **POE SUPPORT:** 24 AWG stranded copper conductors & UL Rated Wiring (E132276-A) supports up to 100W for PoE devices like VOIP phone & security systems; IEEE 802.3bt & DTE power compliance reduces cable heating
- **QUALITY CONSTRUCTION:** UL certified wire; 50-micron gold-plated connectors prevent rust/corrosion to avoid costly network downtime; High quality PVC jacket resists bending or fraying damage
- **EASY INSTALLATION:** 6 inch snagless patch cord for easy installation & flexible disconnection in wiring conduits; Compatible w/Cat5e & earlier standards; Molded boots available for constrained spaces
- **SPECS:** Length: 6in (15cm) Color: White 650 MHz Rated Structure: 4 Pair UTP RJ45 Jacket: PVC Wire Gauge: 24 AWG Copper Wiring: ANSI/T568B Warranty: Lifetime

Hardware

Warranty	Lifetime
Number of Conductors	4 pair UTP
Connector Plating	Gold
Cable Jacket Material	PVC - Polyvinyl Chloride
Fire Rating	CMG Rated (General Purpose)
Cable Type	Snagless
Wiring Standard	TIA/EIA-568-B.1-2001 T568B

Performance

Cable Rating CAT6 - 650 MHz

Connector(s)

Connector A 1 - RJ-45

Connector B 1 - RJ-45

Environmental

Operating Temperature -20C to 80C (-4F to 176F)

Storage Temperature -20C to 80C (-4F to 176F)

Humidity 15 ~ 65%

Physical Characteristics

Color White

Wire Gauge 24 AWG

Conductor Type Stranded Copper

Cable Length 6.0 in [15.2 cm]

Product Length 0.5 ft [0.2 m]

Product Width 0.4 in [1.1 cm]

Product Height 0.6 in [1.4 cm]

Weight of Product 0.5 oz [13.0 g]

Packaging Information

Package Quantity 1

Package Length 8.0 in [20.4 cm]

Package Width 1.5 in [3.7 cm]

Package Height 0.8 in [2.1 cm]

Shipping (Package) Weight 0.8 oz [23.0 g]

What's in the Box

Included in Package 1 - Cat6 patch cable

**Warranty
Information**

Warranty

Lifetime

****Product appearance and specifications are subject to change without notice.***