

1 Port RS232 Serial Ethernet Device Server - PoE Power Over Ethernet

Produkt ID: NETRS2321POE



The NETRS2321POE 1 Port RS232 Serial Ethernet Device Server - PoE (Power Over Ethernet) allows you to install your RS232 devices anywhere on your TCP/IP Ethernet WAN/LAN, and access them as if they were right beside you - even over the Internet!

The Serial Device Server is designed to function seamlessly with your other integrated and add-on serial ports as if they were right inside your computer. Perfect for industrial automation, security, Point of Sale, or any long-range serial application, delivering reliable performance in any environment.

The Ethernet/serial device server supports PoE (Power over Ethernet) when connected to a PoE compliant device - eliminating the need for an external power supply and outlet, and making it easier to situate the device server as needed.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifikat, rapporter och kompatibilitet

Användning

- Manufacturing (CNC machinery, process control equipment, bar code scanners, serial printers)
- Security (UPS control, access key panels, video cameras, card readers)
- Environmental Control (lighting, temperature, clocks)
- POS (credit/debit card readers, receipt printers, bar code scanners, cash registers, scales)

- Hospital (monitoring equipment, nurses' stations)
- Hotel Front Desk (serial printers, bar code scanners, keyboard, mouse, receipt printer, credit/debit card reader)
- Hospitality/Restaurant (credit card/debit card reader, serial printers)

Funktioner

- Supports standard Ethernet or Power over Ethernet (POE)
- Supports UDP, IP, TCP, ICMP, HTTP, DHCP and ARP-Ping protocols
- Wall mountable
- Integrated 10/100Mbps RJ45 LAN port
- Data transfer rates of up to 115.2 Kbps per port
- Supports Auto Crossover (MDI/MDI-X)
- Support for Windows® 2000, XP 32bit, and Vista 32bit

Hårdvara

Garantipolicy	2 Years
Industristandarder	IEEE 802.3af Power-over-Ethernet

Prestanda

Maximal dataöverföringshastighet	115.2Kbps
Databitar	6, 7, 8
Stoppbitar	1, 2
Medeltid mellan fel (MTBF)	233,403 Hours
Stödda protokoll	UDP, IP, TCP, ICMP, HTTP, DHCP, ARP-Ping

Kontakt(er)

Kontakttyp(er)	RJ-45
	DB-9 (9-stifts, D-Sub)



Mjukvara

OS-kompatibilitet	Windows® Vista (32), XP (32), 2000
-------------------	------------------------------------

Särskilda
anmärkningar/
krav

Patents and Licenses	<p>The following patents are licensed for this product. This list might not be all inclusive.</p> <ul style="list-style-type: none"> • United States Patent No. 5,406,260 (expired) • United States Patent No. 6,650,622 • United States Patent No. 7,457,250 • United States Patent No. 8,155,012 • United States Patent No. 8,902,760 • United States Patent No. 8,942,107 • United States Patent No. 9,019,838 • United States Patent No. 9,049,019 • United States Patent Application No. 14/695,456 • United States Patent Application No. 14/726,940
----------------------	--

Indikatorer

LED-indikatorer	Heartbeat, Link/Activity, 10/100 Mbps
-----------------	---------------------------------------

Ström

Power Source	AC-adapter medföljer
Inspänning	100 - 240 AC
Inström	0.3 A
Utspänning	12V DC
Utström	0.1A
Polaritet på mittpol	Positiv
Kontakttyp	M
Strömförbrukning	1.2



Miljö

Drifttemperatur	0°C to 55°C (32°F to 131°F)
Förvaringstemperatur	-20°C to 85°C (-4°F to 185°F)
Luftfuktighet	5~95% RH

Utseende

Färg	Svart
Kabinetttyp	Aluminium
Produktlängd	4.2 in [10.7 cm]
Produktbredd	2.6 in [66.3 mm]
Produkt höjd	1.0 in [25.4 mm]
Produktvikt	9.1 oz [259 g]

Förpackning

Package Length	7.6 in [19.2 cm]
Package Width	11.7 in [29.6 cm]
Package Height	2.8 in [70 mm]
Fraktvikt (förpackning)	34.0 oz [963 g]

Vad det är i lådan

Ingår i paketet	Industrial Serial over IP Device Server
	Universal Power Adapter (NA/UK/EU)
	Instruction Manual

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.

