

2-Port Dual-Monitor DisplayPort KVM Switch, RS232 Serial Control, 4K 60Hz, 2x USB 5Gbps Hub Ports, 2x USB 2.0 HID Ports, Hotkey/Pushbutton Switching, TAA Compliant

Product ID: P2DD46A22-KVM-SWITCH



This Dual-Monitor KVM Switch enables users to switch between two desktops that are USB-A and DisplayPort enabled. It allows for sharing of dual-4K 60Hz DisplayPort monitors, a keyboard and mouse, two USB 5Gbps devices, and two USB 2.0 HID devices.

This 2-Port KVM Switch provides control using serial commands, enabling users to switch between host ports, modify hotkeys, and perform various other functions. The RS232 host ports offer additional flexibility by allowing the switching of an RS232 device between two desktop computers.

DisplayPort EDID and USB Emulation technology enable near-instant switching of a keyboard, video, and mouse. DisplayPort EDID emulation remembers application window placement, while USB Emulation ensures compatibility with combination keyboards/mice, as well as keyboards featuring additional function keys.

This TAA-Compliant KVM Switch supports dual-4K 60Hz DisplayPort monitors, making it an ideal choice for working with high-resolution graphics or video. It also features MST pass-through, enabling the connection of additional monitors through daisy chaining - when using an MST Hub or the Video Output Ports located on the monitor.

This Universal KVM Switch offers multiple switching options, including hotkey, on-screen display, or push-button switching. Hotkeys provide independent switching of USB/Video, Audio, and RS232, allowing for audio playback from one computer while controlling the other or switching without interrupting serial communication. An audible buzzer confirms hotkey input, and LEDs provide a visual indication of the selected host.

Developed to improve performance and security, StarTech.com Connectivity Tools is the only software suite on the market that works with a wide range of IT connectivity accessories. The software suite includes:

- Advanced Windows Layout Utility: Setup and save custom windows layouts.
- MAC Address Pass-Through Utility: Improve network security.

- USB Event Monitoring Utility: Track and log connected USB devices.
- Wi-Fi Auto Switch Utility: Enable users to quickly access faster network speeds via wired LAN.

For more information and to download the StarTech.com Connectivity Tools application, please visit:
www.startech.com/connectivity-tools

Certifications, Reports and Compatibility



Applications

- Switch dual displays, mouse, keyboard, serial, and audio peripherals between two desktop computers
- Great for applications like CAD/CAM, video editing, and content creation

Features

- RS-232 SERIAL CONTROL: Control this 2-Port KVM Switch using serial commands, allowing for switching of host ports, changing hotkeys, and more; Additional DB9 pass-through ports allow the switching of an RS-232 device between two desktop computers
- NEAR INSTANTANEOUS SWITCHING: DisplayPort and USB Emulation enabling seamless switching of a keyboard, video, and mouse between two desktops; EDID Emulation retains window placement while switching; USB Emulation enables combo keyboard/mouse compatibility
- CUSTOMIZABLE SWITCHING: Universal KVM features push-button and hotkey switching; Independent switching of Video, RS-232, and Audio; Listen to audio from one computer while controlling the other, or switch without interrupting RS-232 Serial communication
- DUAL 4K 60HZ MONITORS: KVM Switch supports dual-4K 60Hz DisplayPort monitors, making it ideal for high-resolution applications such as CAD/CAM, video editing, and content creation; Supports MST Pass-through to daisy chain additional monitors
- UNIVERSAL COMPATIBILITY: TAA Compliant KVM Switch works with any operating system including Windows, macOS, and Linux; Compatible with all hardware platforms such as Intel and AMD

Hardware

Warranty

2 Years

Audio	Yes
KVM Ports	2
PC Interface	USB 3.2 Gen 1 (5Gbps)
PC Video Type	DisplayPort
Number of Monitors Supported	2
Rack-Mountable	No
Cables Included	No
Daisy-Chain	No

Performance

On-Screen Display	Yes
Video Revision	DisplayPort 1.2
IP Control	No
Hot-Key Selection	Yes
Maximum Data Transfer Rate	5Gbps
Maximum Digital Resolutions	3840 x 2160 60Hz
Audio Specifications	DisplayPort - 2 Channel Audio Analog Stereo - 2 Channel Audio
Auto Scan	10, 20, 30, 40, 50, and 60 seconds
Port Selection Support	Push Button, Hotkeys, and OSD (On Screen Display)
MTBF	80,907 Hours

Connector(s)

Console Interface(s)	2 - DisplayPort 2 - USB 2.0 Type-A (4 pin, 480Mbps) 2 - USB 3.2 Type-A (9 pin, Gen 1, 5Gbps) 2 - 3.5mm Stereo Female 3 pos
----------------------	---

Host Connectors		1 - DB 9-pin Serial
		1 - Terminal Block (3 Wire)
		1 - Barrel Power Connector (Size N, OD: 5.5, ID: 2.5)
		4 - DisplayPort
		2 - USB 3.2 USB Type-B (9 pin, Gen 1, 5 Gbps)
		4 - 3.5mm Stereo Female 3 pos
Software		
	OS Compatibility	No Drivers or Software
Special Notes / Requirements		
	Note	The DisplayPort source device must support multi-stream transport (MST) for MST Pass-through to work
Indicators		
	LED Indicators	2 - Solid Orange: Port Selected
Power		
	Power Source	AC Adapter Included
	Input Voltage	100 - 240 AC
	Input Current	1 A
	Output Voltage	12V DC
	Output Current	3 A
	Center Tip Polarity	Positive
	Plug Type	N
	Power Consumption (In Watts)	0.1 W
Environmental		
	Operating Temperature	0C to 40C (32F to 104F)
	Storage Temperature	-20C to 60C (-4F to 140F)

Humidity 0% ~ 90% RH (non-condensing)

Physical Characteristics

Color	Black
Material	Steel
	Nickel-plated Zinc
Product Length	10.0 in [25.5 cm]
Product Width	5.1 in [13.0 cm]
Product Height	1.6 in [4.0 cm]
Weight of Product	2.4 lb [1.1 kg]

Packaging Information

Package Length	11.3 in [28.6 cm]
Package Width	11.9 in [30.1 cm]
Package Height	3.2 in [8.1 cm]
Shipping (Package) Weight	3.5 lb [1.6 kg]

What's in the Box

Included in Package	1 - KVM Switch
	1 - Power Supply
	1 - Quick-Start Guide

Warranty Information

Warranty	2 Years
----------	---------

****Product appearance and specifications are subject to change without notice.***