

4-Port DisplayPort KVM Switch, Single 4K 60Hz Monitor, 6x USB Ports, Push-Button & Hotkey Switching, DisplayPort 1.2, OS Independent, TAA Compliant

**Product ID:** P4AD122-KVM-SWITCH



This DisplayPort KVM Switch enables users to switch between four desktops equipped with USB-A and DisplayPort. It facilitates sharing a 4K 60Hz DisplayPort monitor, a keyboard, mouse, two USB 5Gbps devices, a stereo audio output device, and four USB 2.0 devices.

This KVM supports resolutions up to 4K 60Hz, making it ideal for applications such as CAD/CAM, video editing, and content creation. In addition, its support for High Dynamic Range (HDR) enhances contrast, brightness, color, and overall vibrancy.

This universal KVM switch offers hotkey and push-button switching. Hotkeys allow independent switching of audio and video, enabling audio playback from one computer while controlling another. An audible buzzer confirms hotkey inputs, and LEDs provide visual status feedback for the selected host.

The TAA-compliant KVM Switch offers universal compatibility and works with all operating systems, including Windows, macOS, ChromeOS, and Linux. The KVM provides BIOS/UEFI control and is compatible with all hardware platforms, including Intel, AMD, and Apple Silicon (M1/M2/M3).

The rugged metal case helps prevent electromagnetic interference (EMI). 8kV Air/6kV Contact ESD protection enhances the reliability and longevity of the KVM. The included set of rubber feet protect the work surface from scratches and keep KVM in place during operation.

If you'd like to mount this KVM switch to your server rack, we offer a 1U Rackmount Bracket (sold separately) that turns this KVM into a rackmountable KVM.

## Certifications, Reports and Compatibility



## Applications

- Share a monitor, mouse, keyboard, and stereo audio peripheral between four desktop computers
- Great for applications like CAD/CAM, video editing, and content creation

## Features

- **FAST SWITCHING 4K 60HZ KVM:** Control up to four DisplayPort-enabled desktops/workstations/servers from one mouse, keyboard, USB 5Gbps hub, and 4K 60Hz DisplayPort monitor; Ideal for CAD/CAM, video editing, and content creation applications
- **MULTIPLE SWITCHING OPTIONS:** Fast Switching via push-buttons or hotkeys with an audible buzzer providing confirmation; LEDs provide quick visual port selection status; Listen to audio from one computer while controlling another
- **UNIVERSAL COMPATIBILITY:** TAA-Compliant KVM Switch provides BIOS/UEFI control and works with any operating system including Windows, macOS, ChromeOS, and Linux; No software required; Compatible with all hardware platforms such as Intel, AMD, and Apple
- **DURABLE DESIGN:** Metal housing helps prevent Electro-magnetic Interference (EMI); 8kV Air/6kV Contact ESD protection enhances the reliability and longevity of the KVM; Included rubber feet protect the work surface and keep KVM in place during operation
- **TECHNICAL SPECIFICATIONS:** KVM Switch is DisplayPort 1.2 compliant, supporting resolutions up to 4K 60Hz, HDR10, and HDCP 1.4; Supports DisplayPort Audio and 3.5mm analog audio; 4x USB HID Ports; 2x USB 5Gbps Hub Ports; OS Independent

---

### Hardware

Warranty	2 Years
Audio	Yes
KVM Ports	4
PC Interface	USB 3.2 Gen 1 (5Gbps)
PC Video Type	DisplayPort
Number of Monitors	1

Supported	
Cables Included	No
Chipset ID	GL3523

---

**Performance**

On-Screen Display	No
Video Revision	DisplayPort 1.2
IP Control	No
Hot-Key Selection	Yes
Maximum Data Transfer Rate	USB 5Gbps
Maximum Digital Resolutions	4096 x 2160 60Hz
Supported Resolutions	10-bit RGB
	3840x2160 @ 60hz
	3840x2160 @ 30hz
	2560x1600 @ 60hz
	2560x1600 @ 30hz
	2560x1440 @ 60hz
	2048x1536 @ 60hz
	2048x1536 @ 30hz
	1920x1440 @ 60hz
	1920x1200 @ 60hz
	1920x1080 @ 60hz
	1680x1050 @ 60hz
	1600x1200 @ 60hz
	1600x1024 @ 60hz
	1600x900 @ 60hz
	1440x1080 @ 60hz
	1366x768 @ 60hz
	1360x768 @ 60hz

1280x1024 @ 60hz

1280x960 @ 60hz

1280x800 @ 60hz

1280x768 @ 60hz

1280x720 @ 60hz

1176x664 @ 60hz

1152x864 @ 60hz

1024x768 @ 60hz

800x600 @ 60hz

Other resolutions may be supported

Wide Screen Supported Yes

Audio Specifications DisplayPort - 2 Channel Audio

Analog Stereo - 2 Channel Audio

Auto Scan 3, 8, 15 & 30 seconds

Port Selection Support Push Button and Hotkeys

MTBF 130,000 Hours

---

**Connector(s)**

Console Interface(s) 4 - USB 2.0 Type-A (4 pin, 480Mbps)  
2 - USB 3.2 Type-A (9 pin, Gen 1, 5Gbps)  
1 - 3.5mm Stereo Female 3 pos  
1 - DisplayPort  
1 - Barrel Power Connector (Size M, OD:5.50, ID: 2.10)

Host Connectors 4 - DisplayPort  
4 - USB 3.2 Type-B (9 pin, Gen 1, 5Gbps)  
4 - 3.5mm Stereo Female 3 pos

---

**Software**

OS Compatibility No Drivers or Software Required

---

**Indicators**

LED Indicators	4 - Port Selection:  Solid Green - PC 1 ~ 4 connected (powered on)  Solid Red - Selected PC Port  1 - Power LED:  Solid Green - KVM Switch is powered on
----------------	--

---

**Power**

Power Source	AC Adapter Included
Input Voltage	100 - 240 AC
Input Current	1.0A
Output Voltage	12V DC
Output Current	3A
Center Tip Polarity	Positive
Plug Type	M
Power Consumption (In Watts)	36W

---

**Environmental**

Operating Temperature	0C to 40C (32F to 104F)
Storage Temperature	-10C to 60C (14F to 140F)
Humidity	0% ~ 80% RH

---

**Physical Characteristics**

Color	Black
Material	Metal
Product Length	8.7 in [22.0 cm]
Product Width	5.1 in [13.0 cm]
Product Height	1.7 in [4.4 cm]
Weight of Product	2.3 lb [1.0 kg]

---

**Packaging Information**

Package Length	9.7 in [24.6 cm]
Package Width	11.7 in [29.7 cm]
Package Height	3.5 in [8.8 cm]
Shipping (Package) Weight	3.6 lb [1.6 kg]

---

**What's in the Box**

Included in Package	1 - KVM Switch
	1 - Universal Power Adapter (NA/EU/UK/ANZ)
	1 - Set of Rubber Feet
	1 - Quick-Start Guide

---

**Warranty Information**

Warranty	2 Years
----------	---------

---

***\*Product appearance and specifications are subject to change without notice.***