


4 Port RS232 PCI Serial Card Adapter with Power Output

Product ID: PCI4S954PW



The PCI4S954PW 4-Port PCI Serial Card (with Power Output) turns a PCI slot into 4 RS232 (DB9) serial connections and enables compatible devices to draw power from the serial ports.

Suitable for many RS232-powered serial applications, this PCI serial card offers a selectable 5V or 12V power option, capable of power output using pin 1, 4, 8 or 9, which enables you to configure the card to suit the requirements of your powered RS232 devices.

A flexible solution for adding serial ports to full-sized, or small form factor systems, the 4-port serial card includes both low and full profile brackets while the included breakout cable helps to avoid cluttered connections.

Backed by a StarTech.com Lifetime warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Monitor and control industrial machines on an assembly line or in a production environment
- POS retail applications in grocery stores, and any other retail store to control keyboards, cash drawers, receipt printers, card readers/card swipes, scales, and elevated displays on poles
- Bank teller workstations in either full profile or low profile versions to control their serial devices such as cash drawers, card readers / card swipes, printers, keypads / pinpads, pen pads
- Self-service automated machines and kiosks to control serial devices such as scales, touchscreens, magnetic card readers, bar code scanners, receipt printers, label printers
- Used to control multiple surveillance / security cameras in a parking structure, office building, etc.

- Standard ATM automated teller machines to control keypads, receipt printer, card readers / card swipes, touchscreen LCD's, camera control, etc.

Features

- Four high speed RS232 serial ports with data transfer rate up to 460 Kbps
- Selectable voltage output of 5V or 12V
- Selectable power output via pin 1/4/8/9
- Universal PCI card supports installation into 3.3 or 5V PCI slots
- Compliant with PCI specifications revision 3.0
- High Performance Oxford 16C950 UART
- 128-byte deep FIFO per transmitter and receiver
- 15KV ESD protection on all signal pins

Hardware

Warranty	Lifetime
Ports	4
Interface	Serial
Bus Type	PCI / PCI-X (5 / 3.3V)
Card Type	Standard Profile (LP bracket incl.)
Port Style	Dongle (Included)
Industry Standards	PCI 3.0
Chipset ID	PLX/Oxford - OXuPCI954

Performance

Maximum Data Transfer Rate	460.8 Kbps
Serial Protocol	RS-232
Data Bits	5, 6, 7, 8, 9
FIFO	128 Bytes



Flow Control	Automated in-band (Xon/Xoff) Automated out-of-band (CTS#/RTS# and/or DSR#/DTR#)
Stop Bits	1, 1.5, 2
Surge Protection	15KV ESD on all signal pins

Connector(s)

Connector Type(s)	PCI / PCI-X (Universal 3.3 & 5V, 32-bit)
Internal Ports	LP4 (4 pin; Large Drive Power)
External Ports	DB-9 (9 pin, D-Sub)

Software

OS Compatibility	Windows CE 5.0, XP, Vista, 7, 8, 8.1, 10, 11 Windows Server 2003, 2008 R2, 2012, 2012 R2, 2016, 2019 Linux 2.4.x to 4.4.x <i>LTS Versions only</i>
Microsoft WHQL Certified	Yes

Power

Output Voltage	12/5V DC
----------------	----------

Environmental

Operating Temperature	0C to 50C (32F to 122F)
Storage Temperature	-20C to 60C (4F to 140F)
Humidity	5~85% RH

Physical Characteristics

Color	Black
Product Length	5.0 in [12.7 cm]
Product Width	0.6 in [15.0 mm]
Product Height	2.5 in [64.0 mm]
Weight of Product	2.4 oz [68.0 g]

Packaging Information

Package Length	5.9 in [15.0 cm]
----------------	------------------



Package Width	8.3 in [21.0 cm]
Package Height	2.0 in [50.0 mm]
Shipping (Package) Weight	15.0 oz [426.0 g]

What's in the Box

Included in Package	4 Port Serial Card
	Breakout Cable
	Low Profile Bracket
	Driver CD
	Instruction Manual

****Product appearance and specifications are subject to change without notice.***

