


4-Port PCI Express USB 3.0 Card - 2 External, 2 Internal - SATA Power

Product ID: PEXUSB3S2EI



This PCI Express USB 3.0 card offers a cost-effective upgrade that lets you add four USB 3.0 ports to your computer through a PCIe slot. It offers two external ports plus two internal USB 3.0 headers to help adapt your desktop or server to support a variety of USB 3.0 devices.

With extra motherboard-style USB 3.0 headers you have the flexibility to add more internal USB 3.0 devices to your PC. When your existing headers are occupied, you can connect front panel hubs or card readers using this versatile alternative to costly motherboard and computer upgrades.

For added convenience, the card integrates two external USB 3.0 ports, so you can plug in more devices such as external hard drives or printers.

The USB 3.0 card is easy to install and requires no additional drivers or software in natively supported Windows 8.1 / 8 operating systems. Plus, it features a dual profile design that fits in standard or low-profile cases, so you can rest assured it will fit in your small form-factor system if needed.

Connecting older peripherals isn't a problem either. So, there's no need to purchase new devices since the adapter card is backward compatible with your USB 2.0 and 1.x technology.

This high-performance SuperSpeed USB 3.0 card supports data transfer rates up to 5 Gbps and is enhanced with UASP support, which can perform ~70% faster read speed and 40% faster write speed over traditional USB 3.0, when paired with a

The PEXUSB3S2EI is ruggedly built for reliable USB 3.0 device connections and is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Note: UASP (USB Attached SCSI Protocol), is supported in Windows 8, 8.1, Server 2012 and Linux kernel 2.6.37 or later. Test results were obtained using an Intel Ivy Bridge system, StarTech.com add-on USB 3.0 cards, a UASP-enabled StarTech.com enclosure, and a SATA III solid-state drive.

Certifications, Reports and Compatibility

Applications

- Connect external hard drives, tablets, smartphones, CD/DVD drives, MP3 players, printers, scanners, webcams and game controllers to your computer
- Install as a vital hardware component when building your own computer or when upgrading your case

Features


- Flexibility to connect external and internal USB 3.0 devices and supports UASP
- Fast, hassle-free setup with Windows 8 native support, and fits into standard or low-profile systems
- Backward compatibility lets you save money and connect existing USB 2.0 and 1.x devices
- Transfer large files at lightning speed, with throughput support up to 5 Gbps
- Optional SATA power connector provides up to 900mA per port for high-power USB devices
- PCIe x1 interface, compliant with PCI Express 2.0 specifications
- Configured with full-profile bracket, half-height bracket included

Hardware

Warranty	2 Years
Ports	4
Interface	USB 3.0
Bus Type	PCI Express
Card Type	Standard Profile (LP bracket incl.)
Port Style	Integrated on Card
Industry Standards	USB 3.0 Specification Rev. 1.0 PCI Express Base Specification Rev. 2.0 Intel xHCI Specification Rev. 1.0
Chipset ID	Renesas/NEC - PD720201

Performance

Maximum Data Transfer Rate	5 Gbps
----------------------------	--------



Maximum Cable Length	9.8 ft [3 m]
Type and Rate	USB 3.0 - 5 Gbit/s
UASP Support	Yes
MTBF	1,920,042 Hours

Connector(s)

Connector Type(s)	PCI Express x1
Internal Ports	SATA Power (15 pin) IDC (20 pin, USB 3.0, Motherboard Header)
External Ports	USB Type-A (9 pin) USB 3.0 (5 Gbps)

Software

OS Compatibility	Windows XP, Vista, 7, 8, 8.1, 10 Windows Server 2003, 2008 R2, 2012, 2012 R2, 2016, 2019
------------------	---

Special Notes / Requirements

System and Cable Requirements	PCI Express enabled computer with an available PCI Express x1 slot or higher (x4, x8, x16) SATA power connector (recommended, but optional)
Note	The maximum throughput of this card is limited by the bus interface. If used with PCI Express Gen 1.0 enabled computers, the max throughput is 2.5 Gbps. If used with PCI Express Gen 2.0 enabled computers, the max throughput is 5 Gbps.

Environmental

Operating Temperature	5C to 50C (41F to 122F)
Storage Temperature	-25C to 70C (-13F to 158F)
Humidity	20~80% RH

Physical Characteristics

Material	Steel
Product Length	3.6 in [92 mm]



Product Width	0.7 in [18 mm]
Product Height	4.7 in [12 cm]
Weight of Product	1.9 oz [53 g]

Packaging Information

Package Length	5.6 in [14.3 cm]
Package Width	6.9 in [17.4 cm]
Package Height	1.3 in [33 mm]
Shipping (Package) Weight	5.0 oz [143 g]

What's in the Box

Included in Package	4 Port PCI Express USB 3.0 Card - 2 Ext 2 Int
	Low-Profile Bracket
	Driver CD
	Instruction Manual

****Product appearance and specifications are subject to change without notice.***

