

Discontinued and replaced by PEX4S953LP - 4 Port Low Profile Native RS232 PCI Express Serial Card with 16950 UART

Product ID: PEX4S952LP



The PEX4S952LP 4 Port Low Profile Native RS232 PCI Express Serial Card (16950 UART) turns a PCI Express slot into four RS232 (DB9) serial connections.

The card is constructed using a native single chip design that lets you harness the full capability offered by PCI Express (PCIe), while reducing the load applied to the CPU by as much as 48% over conventional bridge chip serial cards.

The PCI Express RS232 Serial Adapter Card is compatible with a broad range of operating systems, including Windows 2000/XP/2003/Vista, Linux Kernel 2.6.11 and up, and ships with a half-height/low profile bracket installed, but also includes an optional full profile bracket that lets you add four serial ports to virtually any computer (regardless of the case form factor).

Backed by a StarTech.com Lifetime warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Bank teller workstations in either full profile or low profile versions to control their serial devices such as cash drawers, card readers / card swipes, printers, keypads / pinpads, pen pads
- POS retail applications in grocery stores, and any other retail store to control keyboards, cash drawers, receipt printers, card readers / card swipes, scales, and elevated displays on poles
- Self service automated machines and kiosks to control serial devices such as scales, touchscreens, magnetic card readers, bar code scanners, receipt printers, label printers

- Standard ATM automated teller machines to control keypads, receipt printer, card readers / card swipes, touchscreen LCD's, camera control, etc.
- Used to control multiple surveillance / security cameras in a parking structure, office building, etc.

Features

- REPLACED BY PEX4S953LP: New version of PEX4S952LP serial controller card offers an ASIX AX99100 chip, 4x DB9 port w/bi-directional RS232 speeds up to 921.6Kbps, 16950 UART, 256 byte FIFO buffer & 9th data bit
- High Performance Dual Channel Oxford 950 UART
- Four high speed RS-232 serial ports with data transfer rate up to 460.8 Kbps
- Half-height mounting bracket installed for low profile cases; includes standard profile bracket
- Native single-Chip, single lane PCI Express
- 128-byte deep FIFO per transmitter and receiver
- Selectable power output on pin 9 for the serial port
- Compliant with PCI Express base specifications revision 1.1a
- Automated in-band software flow control using programmable Xon/Xoff in both directions
- Automated out-of-band hardware flow control using Tx/Rx/RTS/CTS/DSR/DTR/DCD/RI/GND

Hardware

Warranty	Lifetime
Ports	4
Interface	Serial
Bus Type	PCI Express
Card Type	Low Profile (SP bracket incl.)
Port Style	Dongle (Included)
Chipset ID	PLX/Oxford - OXPCle954

Performance

Serial Protocol	RS-232
Max Baud Rate	460.8 Kbps
FIFO	128 Bytes



MTBF 87,600 Hours

Connector(s)

Connector Type(s)	PCI Express x1
Internal Ports	LP4 (4 pin; Large Drive Power)
External Ports	DB-9 (9 pin, D-Sub)

Software

OS Compatibility	Windows CE 6.0/5.0/4.2, 2000, XP, Vista, 7, 8, 8.1, 10 Windows Server 2003, 2008 R2, 2012, 2012 R2, 2016, 2019 Linux 2.4.x to 4.11.x <i>LTS Versions only</i>
Microsoft WHQL Certified	Yes

Environmental

Operating Temperature	-10C to 80C (14F to 176F)
Storage Temperature	-20C to 100C (-4F to 212F)
Humidity	5~85% RH


Physical Characteristics

Product Length	3.5 in [90.0 mm]
Product Width	3.1 in [80.0 mm]
Product Height	0.8 in [20.0 mm]
Weight of Product	2.0 oz [58.0 g]

Packaging Information

Package Length	8.7 in [22.0 cm]
Package Width	5.9 in [15.0 cm]
Package Height	2.2 in [55.0 mm]
Shipping (Package) Weight	14.1 oz [400.0 g]

What's in the Box



Included in Package	4 Port Low Profile Serial Card
	4 Port DB9 Break-out Cable
	Full Profile Bracket
	Driver CD
	Instruction Manual

****Product appearance and specifications are subject to change without notice.***

