

3ft (91cm) Laptop Power Cord, NEMA 1-15P to Right Angle C7, 7A 125V, 18AWG, Laptop Charger Cable, Replacement Power Brick Cord, AC Power Cable, TAA Compliant, UL Listed

Produkt-ID: PXT101NB-STRA-3F



The IT Pro's Choice

StarTech.com power cables are designed by IT professionals. We design our products to meet the technical requirements of a wide variety of applications. Our in-house specialists subject our products to multiple rounds of comprehensive testing, designed to emulate real-world operational conditions. Third-party labs test our products to confirm compliance with the latest safety standards.

StarTech.com manufactures standard and heavy-duty power cords, extension cords, medical-grade cords, power splitter cables, and power cords featuring passthrough outlets. These products are produced in various lengths, with a range of connector ends, jacket types, and wire gauges. Our power cable products are chosen by IT professionals worldwide for the following reasons:.

- Certified for performance and safety - Manufactured using UL listed components to meet UL62 and UL817 compliance standards
- Minimized environmental impact and safe disposal through compliance with REACH and RoHS regulations and guidelines
- 100% copper wiring tested for continuity and conductivity to ensure maximum performance and reliability
- Tested in a temperature chamber to ensure reliable performance over a wide range of environmental conditions

Backed for life by StarTech.com, our brand is trusted throughout the IT ecosystem and used by over 80% of Fortune 500 companies.

Zertifikate Berichte und Kompatibilität



Anwendungen

- Replacement power cord for Laptop power bricks
- 2-prong power cord compatible with LED TVs

Merkmale

- **RIGHT ANGLE CHARGER CORD:** 3ft (0.9m) AC Power Cable with NEMA 1-15P to Right Angle IEC 60320 C7 connector is compatible with laptop chargers and power bricks; 90-degree C7 connector enables quick access in tight spaces; Indoor use; Rated for 125V at 7A
- **BUILT FOR PERFORMANCE AND SAFETY:** Made with UL Listed components; VW-1 Fire Rated cable with fully-molded connector strain reliefs for durability; 2-conductor power cable made with 100% copper wire
- **SPECS:** 3ft (0.9m); TAA Compliant; NEMA 1-15P to Right Angle IEC C7; 18AWG; 125V 7A (Max); Jacket Rating: NISPT-2; Jacket Material: PVC; Color: Black; Temperature Range: -4°F to 221°F (-20 to 105); Cable O.D.: 0.29in (7.3mm)
- **COMPATIBILITY:** NEMA 1-15P plug works with North American outlets; IEC C7 connector works with power bricks for laptops/notebooks, monitors, scanners, printers, and more; Replacement laptop power supply cable/cord
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this laptop charger power cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance; Available in other lengths

Hardware

Garantiebestimmungen Lifetime

Anzahl von Leitern 2

Steckverbinderplatten Nickel

Typ der Kabelummantelung PVC

Feuerwiderstandssklasse Klasse VW-1
e

Steckverbinder

Steckverbinder A	1 - NEMA 1-15 Strom (Nordamerika)
Steckverbinder B	1 - IEC 60320 C7 Strom (unpolarisiert)

Strom

Eingangsspannung	125V AC
Eingangsstrom	7A

Umgebungsbedingungen

Betriebstemperatur	-20° to 105°C (-4° to 221°F)
Lagertemperatur	-20° to 105°C (-4° to 221°F)
Feuchtigkeit	0% to 65% RH

Physische Eigenschaften

Farbe	Schwarz
Steckverbinderart	Gerade auf rechtsgewinkelt
Drahtstärke	18 AWG
Gehäusetyp	PVC
Außendurchmesser des Kabels	0.3 in [7.3 mm]
Produktlänge	36.0 in [91.5 cm]
Produktbreite	1.5 in [3.8 cm]
Produkthöhe	0.7 in [1.9 cm]
Produktgewicht	2.5 oz [70.0 g]

Verpackungsinformationen

Paketlänge	7.6 in [19.3 cm]
------------	------------------

Paketbreite	3.1 in [7.8 cm]
Pakethöhe	1.3 in [3.2 cm]
Versandgewicht (Verpackung)	2.6 oz [74.0 g]

Verpackungsinhalt

Im Paket enthalten	1 - 91cm NEMA 1-15P zu rechtwinkligem C7 Stromkabel
--------------------	---

Garantieinformationen

Warranty	Lifetime
----------	----------

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.