

26U 19" Wall Mount Network Cabinet - 16" Deep Hinged Locking IT Network Switch Depth Enclosure - Assembled Vented Computer Equipment Data Rack w/Shelf & Flexible Side Panels

Product ID: RK2620WALHM



This 26U server or network rack cabinet lets you mount your EIA-310 compliant equipment to the wall, in a secure enclosure that has a hinged rear door for easy access to your equipment. The enclosure features an adjustable mounting depth from 3 to 16 in. to provide a robust storage solution for your rack-mount equipment.

To provide secure stability for your heaviest equipment, this rack offers 4-post mounting, supporting a higher weight capacity per U than 2-post racks and supporting a total load capacity of up to 200 lb. (90 kg).

Save valuable floor space by wall-mounting the enclosure. The wall-mounted design makes this enclosure the ideal solution for optimizing equipment storage in your classroom, retail store, server room or office. This rack also includes a 1U shelf that gives you a stable surface for placing equipment that's not rack-mountable or storing your tools.

The wall-mount network rack makes it easy to access your equipment and cabling, with a rear hinge that swings the enclosure away from the wall. By flipping the enclosure 180 degrees upon installation, you can reverse the direction of the hinge so that the enclosure swings open from left or the right, depending on your preference.

The 26U network cabinet features a removable and reversible front door and removable side panels, each with quick-release mechanisms, so you can easily access your equipment. Plus, each door and panel on this rack features an independent lock, ensuring your equipment is secure.

For hassle-free cable management, the rack includes a 3 meter roll of hook-and-loop cable tie that makes it easy to keep your cables neat and tidy by binding them together or binding them to the rack. The self-gripping fabric can be cut to any size, enabling a wrap-around solution for the cables of any rack-mount equipment.

This server rack enclosure features heavy-duty steel construction, with lockable doors at all entrances. For hassle-free equipment installation, the mounting rails on the rack can be switched for use with square holes and cage nuts, or tapped rails.

To ensure your equipment is running at an optimal temperature, the server rack/cabinet promotes passive cooling. It features mesh doors and vented top and bottom panels for maximum airflow.

For simple and sturdy mounting, the rack's mounting holes are positioned 16 in. apart, so you can securely attach it to a wall using wall studs.

The RK2620WALHMiS backed by a StarTech.com 5-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Wall-mount your server and networking equipment flush against the wall, in areas with limited space such as technology store fronts or repair centers
- Install the rack in your small office environment, where you can't fit a full-sized rack
- Organize cabling or equipment in your network closet, wiring closet, back office or IDF

Features

- **CONVENIENT & SECURE ACCESS:** Wall mount network cabinet w/ 180 hinged design provides easy lockable access to rear of mounted devices. Flexible enclosure also features removable doors & side panels.
- **PRE-ASSEMBLED:** This IT cabinet comes fully assembled out of the box and the included hardware allows for quick installation of server room rackmount or computer equipment without additional purchases
- **DESIGNED FOR COOLING:** The switch depth vented rack has mesh front doors and side panels to provide fresh airflow and supports active cooling with up to four optional 120mm fans (ACFANKIT12)
- **STURDY CONSTRUCTION:** 26U 19" EIA/ECA-310-E enclosed design, 200lb weight capacity, 16" deep with a max. 16" mounting depth, removable sides, locking reversible door, dual top cable hole, optional fans
- **ACCESORIES INCLUDED:** IT Data Rack includes complete set of accessories: a shelf (CABSHELFV1U), roll of hook-and-loop fastener, 50 cage nuts and screws, & 2 pairs of keys for the front and side panels

Hardware	Warranty	5 Years
	Wallmountable	Yes
	Rack Type	4-Post
	Frame Type	Enclosed Cabinet
	U Height	26U
	Special Features	Adjustable Mounting Rails
	Special Features	Built-in Cable Management
	Special Features	Grounding Lug(s)
	Special Features	U-Markings
	Special Features	Wall-Mountable
	Special Features	Ships Fully Assembled
	Mounting Rail Profile	L-Shape

Fan Options Four Optional Fans: 120 mm

Mounting Hole Types Square (For Cage Nut)

Mounting Hole Types Threaded Hole

Industry Standards EIA/ECA-310-E

Performance Weight Capacity 198.9 lb [90 kg]

Special Notes / Requirements Note Includes CABSHELFV1U and 2 pairs of keys

Physical Characteristics

Color Black

Front Door Construction Steel Mesh

Front Door Features Secure Key Lock with Reversible and Removable Front Door

Side Panel Construction Steel Mesh

Side Panel Features Secure Key Lock with Removable Side Panels

Rear Door Construction Steel

Rear Door Features Secure Key Lock

Product Measurements

Internal Width 23.3 in [5.9 cm]

Internal Depth 21.5 in [5.4 cm]

Product Length 21.7 in [5.5 cm]

Product Width 22.8 in [5.8 cm]

Product Height 4.1 ft [1.3 m]

Weight of Product 163.5 lb [74 kg]

Maximum Mounting Depth 15.7 in [4 cm]

Minimum Mounting Depth 2.4 in [60 mm]

Packaging Information

Flat Pack (Assembly Required) No

Package Length 25.6 in [6.5 cm]

Package Width 23.6 in [6 cm]

Package Height 4.6 ft [1.4 m]

Shipping (Package) Weight 165.8 lb [75 kg]



What's in the Box	Included in Package	wall-mount enclosure
	Included in Package	1U shelf
	Included in Package	roll of hook-and-loop fastener
	Included in Package	12-24 cage nuts
	Included in Package	12-24 screws
	Included in Package	door keys
	Included in Package	side panel keys
	Included in Package	instruction manual

****Product appearance and specifications are subject to change without notice.***

