

## 12U Rack Enclosure Server Cabinet - 22 in. Deep - Quiet - Wood Finish

**Product ID:** RKQMCAB12V2



The RKQMCAB12V2 12U Quiet Office Server Cabinet lets you store your server, network or AV equipment discreetly in the office, with a stylish, sound-insulated server cabinet. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

Designed to keep your workspace or boardroom quiet, this server cabinet features top, bottom, and rear foam-insulation for maximum noise reduction. Minimizing operating equipment noise ensures less distraction for you and your colleagues, so you can deploy vital IT hardware even in sound-sensitive environments.

To ensure peak performance from your valuable equipment, the server cabinet offers maximum airflow and a cooler operating environment with an integrated 3-fan (3.5in) module (120 CFM). Plus, this quiet cabinet blends in with your office or boardroom furniture with a stylish wood laminate desktop and a shaded glass front window that keeps your equipment visible for monitoring, as well as front and rear key-locks to prevent unauthorized access.

Providing versatile installation options, this 4-post enclosed cabinet offers adjustable mounting depths from 18in (447mm) to 22in (547mm) to accommodate various sizes of equipment, and supports a weight capacity of up to 600lbs (272kg). The cabinet comes fully assembled, and also features durable casters, so that positioning your server equipment as needed isn't a hassle.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

## Certifications, Reports and Compatibility



## Applications

- Enclose loud equipment and reduce operating noise in sound sensitive areas such as office settings, boardrooms, and classrooms
- Mount server or networking equipment in a well-furnished boardroom
- Add an attractive server cabinet that won't be an eyesore in small / home-office areas with limited space

## Features

- Sound attenuating and quiet 12U enclosed cabinet
- Integrated fan module with (3) 3.5in fans
- TAA compliant for GSA Schedule purchases
- Stylish wood finish desktop with tinted glass front window
- Supports a weight capacity of up to 600lbs (272kg)
- Adjustable mounting depth from 17in (447mm) to 22in (547mm)
- Front and rear key-lock
- Ventilation and rear cable ports with foam grommet kit
- Comes fully assembled
- Casters included

---

## Hardware

Warranty	2 Years
Wallmountable	No
Rack Type	4-Post
Frame Type	Aluminum
U Height	12U
Special Features	Adjustable Mounting Rails
	Castors (Included)
	Ships Fully Assembled
Mounting Rail Profile	G-Shape
Fan Options	Three Fans Included: 92 mm

Mounting Hole Types Square (For Cage Nut)

Industry Standards EIA/ECA-310-E

## Performance

Airflow Rate 40 CFM

Audible Noise 46 dBA @ 1 Meter

Weight Capacity (Stationary) 598.6 lb [271.5 kg]

## Physical Characteristics

Color Dark Gray with Wood Finish Top

Front Door Construction Steel with Glass/Acrylic Window

Front Door Features Secure Key Lock

Side Panel Construction Steel

Rear Door Construction Steel

Rear Door Features Secure Key Lock with Removable Back Door

## Product Measurements

Internal Width 18.6 in [47.2 cm]

Internal Depth 28.4 in [72.1 cm]

Product Length 30.8 in [78.3 cm]

Product Width 27.8 in [70.5 cm]

Product Height 25.3 in [64.2 cm]

Weight of Product 182.0 lb [82.6 kg]

Maximum Mounting Depth 21.6 in [54.8 cm]

Minimum Mounting Depth 14.1 in [35.9 cm]

Product Height with Casters 28.1 in [71.3 cm]

## Packaging Information

Flat Pack (Assembly Required)	No
Package Length	31.3 in [79.5 cm]
Package Width	29.8 in [75.7 cm]
Package Height	34.2 in [86.8 cm]
Shipping (Package) Weight	192.0 lb [87.1 kg]

---

#### What's in the Box

Included in Package	1 - 12U Rack
	4 - Keys (2 Front, 2 Back)
	30 - M6 Screws
	30 - M6 Cage Nuts

---

#### Warranty Information

Warranty	2 Years
----------	---------

---

***\*Product appearance and specifications are subject to change without notice.***