

Industrial Gigabit PoE Injector - High Speed/High Power 90W - 802.3bt PoE++ 52V-56VDC DIN Rail
UPoE/Ultra Power Over Ethernet Injector Adapter -40C to +75C Rugged

Product ID: POEINJ1G90W



This Gigabit Power over Ethernet (PoE+) injector supplies power and data connectivity to a Gigabit PoE-compliant device using a standard Ethernet cable.

Compatible with IEEE 802.3bt and most previous 90W proprietary PoE (Ethernet) standards, including PoH (HDBaseT), Cisco uPoE, Bosch, and AXIS. One product can cover multiple use requirements to improve standardization and deployment and dual power terminal block inputs provide redundancy for critical applications.

As many typical PoE-enabled switches max out at 30W a high 90W power budget is perfect for demanding Type 3 and Type 4 PoE applications like tilt and pan cameras and high power IEEE 802.11ax wireless access points.

Industrial features include -40 C to 75 C operating temperature, IP-30 rated housing, vibration, shock, and free-fall standard testing.

- Vibration: EN 60068-2-6
- Shock: EN 60068-2-27
- Free-fall: EN 60068-2-32

500,000+ hours MTBF rating using Telcordia/Bellcore at 50C for long-term reliability.

The POEINJ1G90W is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

Features

- **WIDE STANDARD COMPATIBILITY:** High speed Industrial Gigabit PoE Injector compatible w/ IEEE 802.3bt (PoE++) & previous 90W proprietary POE standards including PoH (HDBase-T), Cisco uPoE, Bosch & AXIS
- **90W POWER BUDGET:** Provides up to 90W of auto-negotiated power output for Type 3 and Type 4 PoE/Ultra/UPoE applications like tilt and pan cameras and high power IEEE 802.11ax wireless access points
- **TECH SPECS:** 1 Gbps 52V-56VDC Power Input IEEE 802.3af IEEE 802.3at IEEE 802.3bt 90W max PoH (HDBase-T) uPoE 10/100/1000 Mbps Auto Negotiation DIN/Wall Mountable Redundant Power Input
- **ROBUST DESIGN:** Industrial Power over Ethernet Injector w/MTBF of 500,000+hrs @ 50C Vibration, shock & free fall rated Rugged IP-30 aluminum housing Hardened operating temp of -40C to 75C
- **STARTECH.COM ADVANTAGE:** IT professionals' choice for over 30 years This PoE Injector is backed for 2-years by StarTech.com, including free 24/5 North America based multi-lingual tech support

Hardware

| | |
|--------------------|---|
| Warranty | 2 Years |
| Ports | 2 |
| Industry Standards | IEEE 802.3 10BASE-T, IEEE 802.3u 100BASE-TX, IEEE 802.3ab 1000BASE-T, IEEE 802.3at PoE Plus, IEEE 802.3af Power over Ethernet, IEEE 802.3bt |
| Chipset ID | Microsemi PD69204 |

Performance

| | |
|----------------------|------------------|
| Maximum Cable Length | 328.0 ft [100 m] |
| Surge Protection | 2kV, |
| Compatible Networks | 10/100/1000 Mbps |
| Auto MDIX | Yes |
| Full Duplex Support | Yes |
| Jumbo Frame Support | 9K max. |

| | |
|------------------------|--|
| General Specifications | ESD Standard: IEC 61000-4-2: Contact: 6KV; Air: 8KV, EFT Standard: IEC 61000-4-4: Power: 2KV; Signal: 2KV, Surge Standard: IEC 61000-4-5: Power: 2KV; Signal: 2KV, Vibration Standard: EN 60068-2-6, Shock Standard: EN 60068-2-27, Free-Fall Standard: EN 60068-2-32, Housing Standard: IP-30, Safety Standard: EN60950-1 |
| MTBF | 540,891 hours |
| Supported Protocols | CSMA/CD, IEEE 802.3at, IEEE 802.3af, IEEE 802.3bt, |

Connector(s)

| | |
|-------------------|-----------------------------|
| Connector Type(s) | 1 - Ethernet Gigabit |
| | 1 - RJ-45 (PoE+) |
| | 1 - Terminal Block (4 Wire) |

Special Notes / Requirements

| | |
|----------------------|--|
| Patents and Licenses | United States Patent No. 5,406,260 (expired) , United States Patent No. 6,650,622, United States Patent No. 7,457,250, United States Patent No. 8,155,012, United States Patent No. 8,902,760, United States Patent No. 8,942,107, United States Patent No. 9,019,838, United States Patent No. 9,049,019, United States Patent Application No. 14/695,456, United States Patent Application No. 14/726,940, |
|----------------------|--|

Indicators

| | |
|----------------|-----------|
| LED Indicators | 2 - Power |
| | 1 - PoE |

Power

| | |
|-----------|---|
| Plug Type | N |
|-----------|---|

Environmental

| | |
|-----------------------|---------------------------|
| Operating Temperature | -40C to 75C |
| Storage Temperature | -40C to 85C |
| Humidity | 5 to 95% (non-condensing) |

Physical Characteristics

| | |
|--------------|------------------|
| Color | Black |
| Material | Aluminum |
| Cable Length | 328.0 ft [100 m] |



| | |
|-------------------|-------------------|
| Product Length | 3.2 in [81.5 mm] |
| Product Width | 1.3 in [32.0 mm] |
| Product Height | 4.1 in [103.5 mm] |
| Weight of Product | 6.1 oz [174.0 g] |

Packaging Information

| | |
|---------------------------|-------------------|
| Package Quantity | 1 |
| Package Length | 6.4 in [16.2 cm] |
| Package Width | 8.3 in [21.1 cm] |
| Package Height | 2.5 in [6.4 cm] |
| Shipping (Package) Weight | 14.7 oz [416.0 g] |

What's in the Box

| | |
|---------------------|-----------------------------------|
| Included in Package | 1 - Industrial-Grade PoE Injector |
| | 1 - Terminal Block |
| | 1 - Mounting Hardware Kit |
| | 1 - Quick-Start Guide |

****Product appearance and specifications are subject to change without notice.***

