

2.5" SATA USM™; Enclosure for S2510U33RUSM USM Bay with External USB 3.0 Adapter

Produkt ID: S2510U33USM



The S2510U33USM USM enclosure enables you to insert a 2.5" SATA HDD/SSD into any USM host interface including the StarTech.com S2510U33RUSM 5.25" USM bay, and Seagate GoFlex® devices. To ensure you get the most from your SATA III drive, the enclosure supports transfer speeds up to 6.0 Gbps.

USM (Universal Storage Module) is a portable drive standard that interfaces with SATA and enables you to hot-swap drives between multiple host devices, such as PCs, notebooks, DVRs and many others.

Using the included USM to USB 3.0 adapter the enclosure can also be connected externally to non-USM host devices via USB. Plus, with support for UASP, the enclosure performs up to 70% faster than conventional USB when paired with a UASP-enabled host controller to utilize the full potential of your SATA III hard drives. See our UASP testing results below for further details.

To ensure compatibility with your computer system, the S2510U33USM supports all of the leading operating systems, including: Microsoft Windows® (8/7/Vista/XP/Server 2008/Server 2003), Apple® OSX (10.9/10.8/10.7/10.6), Linux, and Google Chrome OS™.


The S2510U33USM is backed by a StarTech.com 2-year warranty and free lifetime technical support.

UASP is supported in Windows 8, Mac (OSX 10.8 or above), and Linux. In testing UASP performs with a 70% faster read speed and 40% faster write speed over traditional USB 3.0 at peak performance.

At the same peak in testing UASP also shows an 80% reduction in required processor resources.

Testing results were obtained using an Intel® Ivy Bridge system, a UASP enabled StarTech.com enclosure, and a SATA III solid state drive.

Certifikat, rapporter och kompatibilitet



Användning

- Create a fast, portable external storage solution for desktops, laptops or netbooks
- Add-on extra storage to almost any USB-enabled computer system
- Back up your important data to an external storage device
- Share large files between computers quickly and securely, without a network

Funktioner

- Designed for Front-Mount Installation with S2510U33RUSM 5.25" USM Bay
- Fully compatible with Seagate GoFlex®, and other USM devices
- USB 3.0 to USM Enclosure Adapter Included
- UASP Compliant
- SuperSpeed USB 3.0 compliant host interface supporting data transfer rates up to 5Gbps
- Compatible with SATA revision I/II/III (1.5/3.0/6.0 Gbps)
- Supports 2.5" form factor SATA hard drives (HDD) and solid state drives (SSD)
- Plug-and-Play and Hot-Swap compatible
- UL94 V0 Flammability rating

Hårdvara

Garantipolicy	2 Years
Gränssnitt	SATA

		USB 3.2 Gen 1 (5 Gbps)
	Antal enheter	1
	Enhetsstorlek	2.5in
	Enhetstyp	SATA
	Enhetsinstallation	Fixerad
	Chipset-ID	ASMedia - ASM1053 - 6G
Prestanda		
	Typ och hastighet	USB 3.0 - 5 Gbit/s
	UASP-stöd	Ja
	Typ och hastighet	SATA III (6 Gbps)
	Allmänna specifikationer	UL94 V0 Flammability rating
Kontakt(er)		
	Enhetskontakter	1 - SATA data- & ström-kombo (7+15-stifts)
	Värdkontakter	1 - USM (22-stifts SATA data & ström)
		USB 3.2 Type-B (9 stift, Gen 1, 5 Gbps)
		1 - USB 3.0 Micro-B (10-stifts, SuperSpeed)
Mjukvara		
	OS-kompatibilitet	OS independent; No software or drivers required
Indikatorer		
	LED-indikatorer	1 - Hard Drive Power/Activity (Enclosure)
Miljö		
	Drifttemperatur	0°C to 40°C (32°F to 104°F)
	Förvaringstemperatur	-20°C to 70°C (-4°F to 158°F)
	Luftfuktighet	10% ~ 90% RH

Utseende

Färg	Svart
Kabinetttyp	Aluminium och plast
Produktlängd	4.7 in [12 cm]
Produktbredd	3.2 in [8.1 cm]
Produkthöjd	0.4 in [0.9 cm]
Produktvikt	3.3 oz [93.2 g]

Förpackning

Förpackningsantal	1
Paketets längd	6.9 in [17.5 cm]
Paketets bredd	5.1 in [13 cm]
Paketets höjd	1.6 in [40 mm]
Fraktvikt (förpackning)	7.6 oz [214.5 g]

Vad det är i lådan

Ingår i paketet	1 - 2.5" USM HDD Enclosure
	1 - USM to USB 3.0 interface adapter
	1 - Micro USB 3.0 Cable
	1 - Instruction Manual

Warranty Information

Warranty	2 År
----------	------

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.